



SCHUNK chuck jaws for HG-F 630



Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Screws	m/set [kg]
	SFG 630	0157106	40	24	65	58	230	82	M20	17.1

Hard Stepped Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 630	0155106	24	40	65	105	97	185	30	82	M20	Steel	18

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 630	0153106	24	40	65	118	110	260	70	82	M20	Steel	39.6
	SFA-AL 630	0172106	24	40	65	118	110	260	70	82	M20	Aluminum	14.8



Technical advice and sales: Tel. +49-7133-103-2750