



SCHUNK chuck jaws for KNCS-2G 400-128


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	36 - 166	450	II	SZKA-ST 311	0182156	12	26	32	50	40	54	M12	Steel	2.2


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	104 - 256	449	I	SZKI 319	0166162	12	26	40	53	25	M8	54	M12	Steel	3.9
	201 - 365	449	I	SZKI 322	0166165	12	26	40	53	25	M8	54	M12	Steel	2.7
	103 - 178	449	II	SZKI 319	0166162	12	26	40	53	25	M8	54	M12	Steel	3.9
	124 - 287	449	II	SZKI 322	0166165	12	26	40	53	25	M8	54	M12	Steel	2.7

Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	96 - 259	450	I	SZKA 321	0139166	12	26	40	53	25	M8	54	M12	Steel	3.1
	204 - 368	458	I	SZKA 324	0139169	12	26	40	53	25	M8	54	M12	Steel	2.8
	53 - 182	450	II	SZKA 321	0139166	12	26	40	53	25	M8	54	M12	Steel	3.1
	126 - 290	450	II	SZKA 324	0139169	12	26	40	53	25	M8	54	M12	Steel	2.8

Pendulum jaws

	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	108 - 197	377	PNK-G 400-2	0190619	99	50	3.7
	180 - 279	474	PNK-G 400-4	0190621	99	50	4.8
	228 - 344	513	PNK-G 400-6	0190623	99	50	5.28



Technical advice and sales: Tel. +49-7133-103-2750