



SCHUNK chuck jaws for KNCS-2G 225-66


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	25 - 90	268	II	SZKA-ST 201	0182152	10	20	22	45	37	40	M8	Steel	0.9


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	60 - 115	269	I	SZKI 209	0166154	10	20	30	45	20	M6	40	M8	Steel	1.7
	111 - 185	269	I	SZKI 211	0166156	10	20	30	45	20	M6	40	M8	Steel	1.4
	59 - 77	267	II	SZKI 209	0166154	10	20	30	45	20	M6	40	M8	Steel	1.7
	91 - 147	267	II	SZKI 211	0166156	10	20	30	45	20	M6	40	M8	Steel	1.4


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	37 - 102	269	I	SZKA 212	0139153	10	20	26	45	25	M6	40	M8	Steel	1.4
	103 - 177	270	I	SZKA 213	0139154	10	20	30	45	25	M6	40	M8	Steel	1.3
	137 - 212	276	I	SZKA 216	0139159	10	20	30	45	25	M6	40	M8	Steel	1.2
	36 - 63	268	II	SZKA 212	0139153	10	20	26	45	25	M6	40	M8	Steel	1.4
	74 - 138	268	II	SZKA 213	0139154	10	20	30	45	25	M6	40	M8	Steel	1.3
	108 - 173	268	II	SZKA 216	0139159	10	20	30	45	25	M6	40	M8	Steel	1.2

Pendulum jaws

	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	53 - 87	226	PNK-G 200-2	0190659	76	36	1.2
	86 - 141	267	PNK-G 200-6	0190663	76	36	1.6
	105 - 171	265	PNK-G 200-8	0190665	76	36	1.8

Soft Monoblock Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	Material	m/set [kg]
	UVB-HS 200	0164119	22	85	60	29	84	Steel	2.67



Technical advice and sales: Tel. +49-7133-103-2750