



SCHUNK chuck jaws for CL-D 200


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	17 - 169	56	SZA-ST 25-2	0175103	21	45	50	40	28	M16	Steel	2.7
	20 - 202	61	SZA-ST 31-1	0175104	21	45	50	40	28	M16	Steel	3.3


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	80 - 117	62	SZI 25-34	0123183	21	50	58	25	M8	28	M16	Steel	3.5
	80 - 146	68	SZI 31-11	0123186	21	50	58	25	M8	28	M16	Steel	4.1

Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	40 - 141	58	SZA 25-37	0138180	21	50	58	25	M8	28	M16	Steel	3.3
	68 - 103	58	SZA 25-38	0138181	21	50	58	25	M8	28	M16	Steel	2.9
	46 - 163	64	SZA 31-10	0138184	21	50	58	25	M8	28	M16	Steel	3.4
	66 - 111	65	SZA 31-11	0138185	21	50	58	25	M8	28	M16	Steel	3.4

Jaw blanks





	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Min. distance a [mm]	Min. distance b [mm]	Screws	Material	m/piece [kg]
	SBM 42	0112113	21	50	60	105	15	28	M16	Steel	2.4
	SBM 4210	0112115	21	50	100	120	15	28	M16	Steel	5
	SBM 4212	0112116	21	50	120	120	15	28	M16	Steel	5.6
	SBM 4215	0112117	21	50	150	120	15	28	M16	Steel	7
	SBM 428	0112114	21	50	80	120	15	28	M16	Steel	3.7
	SBM 4281	0112137	21	50	80	150	15	28	M16	Steel	4.6



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for CL-D 200

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWBL 250-21	0120155	21	50	50	120	4	20	28	M16	Steel	5.6
	2 SWK 200	0126102	21	80	80	95		22	28	M16	Steel	8.2
	SWB 250	0120105	21	50	80	120		30	28	M16	Steel	9.4
	SWB-AL 250	0168102	21	50	80	120		30	28	M16	Aluminum	3

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NS 163	0142102	21	25.5	11	M16	M16 x 35	150



Technical advice and sales: Tel. +49-7133-103-2750