



SCHUNK chuck jaws for KNCS-N 140


Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Screws	m/set [kg]
	GBK 140	0159099	18	8	20	27.5	56	32	M8	0.4
	GBK-V 140	0159157	18	8	20	27.5	56	32	M8	0.4


Hard Stepped Block Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Material	m/set [kg]
	GST 140-160 I	0162097	20	43.5	22	58	7	Steel	0.7
	GST 140-160 II	0162098	20	43.5	22	58	7	Steel	0.7

Soft Monoblock Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	Material	m/set [kg]
	UVB 160	0164106	20	55.5	35	65	Steel	1.6

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 140	0153098	8	18	20	40	36		69	25	32	M8	Steel	0.9
	SFA 140-C1	0154129	8	18	30		45	41	63	19	32	M8	Steel	1.7



Technical advice and sales: Tel. +49-7133-103-2750