



SCHUNK Spannbacken für GHDN 250


Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Min. Abstand a (Backen- spitze bis erste Bohrung) [mm]	Min. Abstand b (Erste bis zweite Bohrung) [mm]	Schrauben	Werkstoff	m/Stück [kg]
	SBM 41	0112112	21	50	60	90	15	28	M16	Stahl	2.1
	SBM 42	0112113	21	50	60	105	15	28	M16	Stahl	2.4
	SBM 4210	0112115	21	50	100	120	15	28	M16	Stahl	5
	SBM 4212	0112116	21	50	120	120	15	28	M16	Stahl	5.6
	SBM 4215	0112117	21	50	150	120	15	28	M16	Stahl	7
	SBM 428	0112114	21	50	80	120	15	28	M16	Stahl	3.7
	SBM 4281	0112137	21	50	80	150	15	28	M16	Stahl	4.6
	SBM 43	0112118	21	60	60	90	15	28	M16	Stahl	2.4
	SBM 44	0112119	21	60	60	105	15	28	M16	Stahl	2.9
	SBM 45	0112120	21	60	80	90	15	28	M16	Stahl	3.2
	SBM 46	0112121	21	60	80	105	15	28	M16	Stahl	3.8
	SBM 47	0112122	21	60	80	120	15	28	M16	Stahl	4.4
	SBM 48	0112123	21	80	60	90	15	28	M16	Stahl	3.2
	SBM 498	0112125	21	80	80	120	15	28	M16	Stahl	5.8


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB 250	0121105	21	50	58	103.5	14	34	25	25	M16	Stahl	3.5

Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	47 - 95	263	SZA 25-37	0138180	21	50	58	25	M8	28	M16	Stahl	3.3
	87 - 135	263	SZA 25-38	0138181	21	50	58	25	M8	28	M16	Stahl	2.9
	136 - 185	265	SZA 25-39	0138182	21	50	58	25	M8	28	M16	Stahl	2.7
	183 - 232	302	SZA 25-40	0138183	21	50	58	25	M8	28	M16	Stahl	3.2


Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	78 - 123	268	SZI 25-34	0123183	21	50	58	25	M8	28	M16	Stahl	3.5
	118 - 164	270	SZI 25-35	0123184	21	50	58	25	M8	28	M16	Stahl	3.2
	163 - 210	270	SZI 25-36	0123185	21	50	58	25	M8	28	M16	Stahl	3







Technische Beratung und Verkauf: Tel. +49-7133-103-2750



Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	18 - 54	255	SZA-ST 25-2	0175103	21	45	50	40	28	M16	Stahl	2.7

QUENTES Kunststoffbacken



	Spannbereich ØD	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Max. Anzugsmo- ment [Nm]	Schrauben	m/Satz [kg]
	28 - 80	TRQ 250-1	0150003	21	45	57	93	28		M16	0.97
	139 - 216	TRQ 250-2	0150004	21	45	67	94	28		M16	1.24
		QUINTES 10-3	0150100						8		
		QUINTES 20-3	0150200						8		

Segmentbacken




	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWB-SM 250-21	0169103	21	180	104	250	70	55	80	30	28	M16	Stahl	14
	SWB-SM 251	0169107	21	180	104	250	100	85	80	30	28	M16	Stahl	21.7
	SWB-SA 250-21	0170103	21	180	70	250	78	63	87.5	40	28	M16	Aluminium	7.3
	SWB-SA 251	0170107	21	180	70	250	100	85	87.5	40	28	M16	Aluminium	8.3



Verzahnte Stangen

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	SBM-ST 210	0112180	21	50	60	420	Stahl	9.4
	SBM-ST 211	0112181	21	50	80	420	Stahl	12.7
	SBM-ST 212	0112182	21	50	120	420	Stahl	19.3
	SBM-ST 213	0112183	21	80	80	420	Stahl	20.4
	SBM-STA 210	0112184	21	50	80	420	Aluminium	4.6

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWBL 250-21	0120155	21	50	50	120	4	20	28	M16	Stahl	5.6
	SWBL 315	0120156	21	50	50	140	4	30	28	M16	Stahl	6.5
	CWB 251	0100012	21	50	60	95		15	28	M16	Stahl	5.2
	SWB 250	0120105	21	50	80	120		30	28	M16	Stahl	9.4
	SWB-AL 250	0168102	21	50	80	120		30	28	M16	Aluminium	3

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmoment [Nm]
	NS 163	0142102	21	25.5	11	M16	M16 x 35	150

