



SCHUNK Spannbacken für GH-M 400



Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Min. Abstand a (Backen- spitze bis erste Bohrung) [mm]	Min. Abstand b (Erste bis zweite Bohrung) [mm]	Schrauben	Werkstoff	m/Stück [kg]
	JBM 120	0114420	21	50	60	130	15	30	M16	Stahl	3.1
	JBM 121	0114421	21	50	80	130	15	30	M16	Stahl	4.1
	JBM 122	0114422	21	50	120	130	15	30	M16	Stahl	6
	JBM 123	0114423	21	58	150	130	15	30	M16	Stahl	8.8
	JBM 124	0114424	21	80	80	130	15	30	M16	Stahl	6.2

Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB-J 126	0133105	21	50	62	128	14	46	30	30	M16	Stahl	5.15
	SHB-J 122	0133113	21	50	52	104	18	20	30	30	M16	Stahl	3.3

Verzahnte Stangen




	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	JBM-ST 210	0114540	21	50	80	420	Stahl	12.7
	JBM-ST 211	0114541	21	60	120	420	Stahl	23.2
	JBM-STA 210	0114542	21	50	80	420	Aluminium	4.6



Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für GH-M 400

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	KM-WBL 121	0132604	21	50	50	145	10	30	30	M16	Stahl	6.9
	KM-WBL 125	0132618	21	50	100	145	10	30	30	M16	Stahl	14.2
	KM-WB 126	0132131	21	50	60	129		39	30	M16	Stahl	7.8
	KM-WB 127	0132148	21	50	100	140		39	30	M16	Stahl	13.8
	KM-WB 128	0132154	21	50	80	129		39	30	M16	Stahl	10.4
	KM-WBAL 121	0132525	21	50	80	130		40	30	M16	Aluminium	3.8

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmoment [Nm]
	NS 163	0142102	21	25.5	11	M16	M16 x 35	150



Technische Beratung und Verkauf: Tel. +49-7133-103-2750