




# SCHUNK chuck jaws for GH-M 400



## Hard Stepped Top Jaws

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|--------|----------|---------------|
|  | SHB-J 126   | 0133105 | 21        | 50        | 62        | 128       | 14        | 46        | 30        | 30        | M16    | Steel    | 5.15          |
|  | SHB-J 122   | 0133113 | 21        | 50        | 52        | 104       | 18        | 20        | 30        | 30        | M16    | Steel    | 3.3           |




## Jaw blanks

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Min. distance<br>a<br>[mm] | Min. distance<br>b<br>[mm] | Screws | Material | m/piece<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|----------------------------|----------------------------|--------|----------|-----------------|
|  | JBM 120     | 0114420 | 21        | 50        | 60        | 130       | 15                         | 30                         | M16    | Steel    | 3.1             |
|                                                                                   | JBM 121     | 0114421 | 21        | 50        | 80        | 130       | 15                         | 30                         | M16    | Steel    | 4.1             |
|                                                                                   | JBM 122     | 0114422 | 21        | 50        | 120       | 130       | 15                         | 30                         | M16    | Steel    | 6               |
|                                                                                   | JBM 123     | 0114423 | 21        | 58        | 150       | 130       | 15                         | 30                         | M16    | Steel    | 8.8             |
|                                                                                   | JBM 124     | 0114424 | 21        | 80        | 80        | 130       | 15                         | 30                         | M16    | Steel    | 6.2             |

## Serrated bars

|                                                                                     | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Material | m/piece<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|----------|-----------------|
|  | JBM-ST 210  | 0114540 | 21        | 50        | 80        | 420       | Steel    | 12.7            |
|                                                                                     | JBM-ST 211  | 0114541 | 21        | 60        | 120       | 420       | Steel    | 23.2            |
|  | JBM-STA 210 | 0114542 | 21        | 50        | 80        | 420       | Aluminum | 4.6             |

## Soft Top Jaws

|                                                                                     | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a1<br>[mm] | a<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|------------|-----------|-----------|--------|----------|---------------|
|  | KM-WBL 121  | 0132604 | 21        | 50        | 50        | 145       | 10         | 30        | 30        | M16    | Steel    | 6.9           |
|                                                                                     | KM-WBL 125  | 0132618 | 21        | 50        | 100       | 145       | 10         | 30        | 30        | M16    | Steel    | 14.2          |
|  | KM-WB 126   | 0132131 | 21        | 50        | 60        | 129       |            | 39        | 30        | M16    | Steel    | 7.8           |
|                                                                                     | KM-WB 127   | 0132148 | 21        | 50        | 100       | 140       |            | 39        | 30        | M16    | Steel    | 13.8          |
|                                                                                     | KM-WB 128   | 0132154 | 21        | 50        | 80        | 129       |            | 39        | 30        | M16    | Steel    | 10.4          |
|  | KM-WBAL 121 | 0132525 | 21        | 50        | 80        | 130       |            | 40        | 30        | M16    | Aluminum | 3.8           |



Technical advice and sales: Tel. +49-7133-103-2750

# SCHUNK chuck jaws for GH-M 400

## T-nut

|                                                                                   | Description | ID      | S<br>[mm] | H<br>[mm] | H1<br>[mm] | G   | Cyl.-screw | Max. adm.<br>tightening torque<br>[Nm] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-----|------------|----------------------------------------|
|  | NS 163      | 0142102 | 21        | 25.5      | 11         | M16 | M16 x 35   | 150                                    |



Technical advice and sales: Tel. +49-7133-103-2750