



SCHUNK chuck jaws for NTL-M 400


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	99 - 191	421	SZIJ 38-1	0179132	22	60	85	33	M8	43	M20	Steel	9.5
	144 - 247	425	SZIJ 38-2	0179133	22	60	85	33	M8	43	M20	Steel	9.1
	199 - 302	420	SZIJ 38-3	0179134	22	60	85	33	M8	43	M20	Steel	7.6
	268 - 372	430	SZIJ 38-4	0179135	22	60	85	33	M8	43	M20	Steel	7.1
	328 - 432	481	SZIJ 38-5	0179136	22	60	85	33	M8	43	M20	Steel	8.6


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	46 - 135	423	SZAJ 38-1	0138135	22	60	85	33	M8	43	M20	Steel	10.2
	91 - 193	428	SZAJ 38-2	0138136	22	60	85	33	M8	43	M20	Steel	9
	150 - 253	428	SZAJ 38-3	0138137	22	60	85	33	M8	43	M20	Steel	7.5
	211 - 314	447	SZAJ 38-4	0138138	22	60	85	33	M8	43	M20	Steel	7.5
	271 - 374	465	SZAJ 38-5	0138139	22	60	85	33	M8	43	M20	Steel	8.2
	330 - 434	517	SZAJ 38-6	0138140	22	60	85	33	M8	43	M20	Steel	9.5

Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB-J 150	0133114	22	60	86	143	20	27	43	43	M20	Steel	9

Serrated bars




	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	JBM-ST 220	0114550	22	60	120	420	Steel	23.2
	JBM-STA 220	0114552	22	60	100	420	Aluminum	7



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for NTL-M 400

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	KM-WBL 150	0132605	22	60	60	185	10	30	43	M20	Steel	12.6
	KM-WB 151	0132112	22	60	80	156		36	60	M20	Steel	14.5
	KM-WB 153	0132132	22	60	80	165		37	43	M20	Steel	16.1
	KM-WB 155	0132156	22	60	120	165		37	43	M20	Steel	24.2
	KM-WBAL 150	0132526	22	60	80	145		30	43	M20	Aluminum	5.1
												



Technical advice and sales: Tel. +49-7133-103-2750