



SCHUNK Spannbacken für HG-2G 400-128


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	90 - 232	423	I	SZKA 321	0139166	12	26	40	53	25	M8	54	M12	Stahl	3.1
	198 - 341	431	I	SZKA 324	0139169	12	26	40	53	25	M8	54	M12	Stahl	2.8
	48 - 155	423	II	SZKA 321	0139166	12	26	40	53	25	M8	54	M12	Stahl	3.1
	131 - 263	423	II	SZKA 324	0139169	12	26	40	53	25	M8	54	M12	Stahl	2.8


Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	98 - 229	422	I	SZKI 319	0166162	12	26	40	53	25	M8	54	M12	Stahl	3.9
	195 - 338	422	I	SZKI 322	0166165	12	26	40	53	25	M8	54	M12	Stahl	2.7
	97 - 152	422	II	SZKI 319	0166162	12	26	40	53	25	M8	54	M12	Stahl	3.9
	128 - 260	422	II	SZKI 322	0166165	12	26	40	53	25	M8	54	M12	Stahl	2.7

Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	30 - 140	423	II	SZKA-ST 311	0182156	12	26	32	50	40	54	M12	Stahl	2.2

Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	108 - 196	377	PNK-G 400-2	0190619	99	50	3.7
	180 - 279	473	PNK-G 400-4	0190621	99	50	4.8
	228 - 328	494	PNK-G 400-6	0190623	99	50	5.28



Technische Beratung und Verkauf: Tel. +49-7133-103-2750