



SCHUNK Spannbacken für HG-2G 630-254


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	217 - 461	683	I	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Stahl	6
	319 - 563	683	I	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Stahl	5.1
	52 - 262	682	II	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Stahl	6
	135 - 364	683	II	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Stahl	5.1

Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	247 - 291	683	I	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Stahl	6
	337 - 582	682	I	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Stahl	5.5
	106 - 292	681	II	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Stahl	6
	167 - 382	681	II	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Stahl	5.5

Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	163 - 276	563	PNK-G 630-2	0190635	118	50	7.9
	228 - 341	603	PNK-G 630-4	0190637	118	50	8.3
	329 - 479	663	PNK-G 630-6	0190639	118	50	10.4
	397 - 532	727	PNK-G 630-8	0190641	118	50	12



Technische Beratung und Verkauf: Tel. +49-7133-103-2750