




# SCHUNK Spannbacken für RMG 250


## Grundbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | S<br>[mm] | B<br>[mm] | B1<br>[mm] | H<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|------------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | GBK 250     | 0159101    | 20        | 12        | 26        |            | 37        | 104       |           | 40        | M12       | 1.8            |
|                                                                                   | GBKL 250    | 0159121    | 20        | 12        | 26        |            | 37        | 125       |           | 40        | M12       | 2.4            |
|                                                                                   | GBK-V 250   | 0159151    | 20        | 12        | 26        |            | 37        | 104       |           | 40        | M12       | 1.8            |
|  | STB-G 250-2 | 0160657    | 21        |           | 26        | 50         | 71        | 104       |           |           | M16       | 5.2            |
|  | STN 250-5   | 0160651    | 16        |           | 26        | 40         | 49        | 110       | 10        | 30        | M12       | 2.9            |
|                                                                                   | STN 250-5   | 0160600    | 17        |           | 26        | 40         | 48        | 86        | 10        | 22        | M12       | 2.6            |
|                                                                                   | STN 250-6   | 0160601    | 21        |           | 26        | 45         | 52        | 110       | 13        | 28        | M16       | 4              |



## Harte Stufenaufsatzbacken

|                                                                                    | Bezeichnung | Ident.-Nr. | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | T<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|------------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SHF 250     | 0155102    | 12        | 20        | 30        | 55        | 50         | 90        | 14        | 40        | M12       | Stahl     | 1.9            |

## Harte Stufenblockbacken

|                                                                                     | Bezeichnung | Ident.-Nr. | B<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | T<br>[mm] | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|------------|-----------|-----------|-----------|----------------|
|  | GST 251     | 0162105    | 26        | 65        | 36         | 107.5     | 10        | Stahl     | 2.8            |

## Segmentbacken



|                                                                                     | Bezeichnung | Ident.-Nr. | N<br>[mm] | S<br>[mm] | B<br>[mm] | B1<br>[mm] | Ø D<br>[mm] | H<br>[mm] | H1<br>[mm] | H2<br>[mm] | L<br>[mm] | L1<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|------------|-------------|-----------|------------|------------|-----------|------------|-----------|-----------|-----------|----------------|
|  | SFA-SM 250  | 0173102    | 12        | 20        | 180       | 70         | 250         | 60        | 55         | 45         | 90        | 44         | 40        | M12       | Stahl     | 12.8           |
|                                                                                     | SFA-SM 251  | 0173106    | 12        | 20        | 180       | 70         | 250         | 80        | 75         | 65         | 90        | 44         | 40        | M12       | Stahl     | 16.8           |
|  | SFA-SA 250  | 0174102    | 12        | 20        | 180       | 70         | 250         | 58        | 53         | 43         | 87.5      | 44         | 40        | M12       | Aluminium | 4.8            |
|                                                                                     | SFA-SA 251  | 0174106    | 12        | 20        | 180       | 70         | 250         | 80        | 75         | 65         | 87.5      | 44         | 40        | M12       | Aluminium | 6.4            |






Technische Beratung und Verkauf: Tel. +49-7133-103-2750

# SCHUNK Spannbacken für RMG 250

## Weiche Aufsatzbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | H1<br>[mm] | H2<br>[mm] | L<br>[mm] | L1<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|------------|------------|-----------|------------|-----------|-----------|-----------|----------------|
|  | SFA 250     | 0153102    | 12        | 20        | 30        | 55.5      | 50.5       |            | 125       | 35         | 40        | M12       | Stahl     | 3.7            |
|                                                                                   | SFA 250-C1  | 0154101    | 12        | 20        | 40        |           | 60         | 55         | 90        | 26         | 40        | M12       | Stahl     | 3.9            |
|                                                                                   | SFA 250-C2  | 0154102    | 12        | 20        | 40        |           | 60         | 55         | 125       | 26         | 40        | M12       | Stahl     | 5.6            |
|                                                                                   | SFA 250-C3  | 0154103    | 12        | 20        | 40        |           | 80         | 75         | 125       | 26         | 40        | M12       | Stahl     | 7.7            |
|                                                                                   | SFA 250-C4  | 0154104    | 12        | 20        | 40        |           | 100        | 95         | 125       | 26         | 40        | M12       | Stahl     | 9.8            |
|                                                                                   | SFA 250-C5  | 0154105    | 12        | 20        | 40        |           | 120        | 115        | 125       | 26         | 40        | M12       | Stahl     | 11.8           |
|                                                                                   | SFA 250-C6  | 0154106    | 12        | 20        | 60        |           | 60         | 55         | 90        | 26         | 40        | M12       | Stahl     | 6              |
|                                                                                   | SFA 250-C7  | 0154107    | 12        | 20        | 80        |           | 60         | 55         | 90        | 26         | 40        | M12       | Stahl     | 8.5            |
|                                                                                   | SFA 250-C8  | 0154134    | 12        | 20        | 80        |           | 100        | 95         | 125       | 26         | 40        | M12       | Stahl     | 20.9           |
|  | SFA-AL 250  | 0172103    | 12        | 20        | 40        | 60        | 55         |            | 125       | 35         | 40        | M12       | Aluminium | 2.1            |

## Weiche Blockbacken

|                                                                                     | Bezeichnung | Ident.-Nr. | B<br>[mm] | B1<br>[mm] | H<br>[mm] | H1<br>[mm] | H2<br>[mm] | L<br>[mm] | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|------------|-----------|------------|------------|-----------|-----------|----------------|
|   | UVB 250     | 0164101    | 26        |            | 84        | 55         |            | 99        | Stahl     | 4.8            |
|                                                                                     | UVB-H 250   | 0164117    | 26        |            | 115       | 86         |            | 99        | Stahl     | 6.6            |
|  | UVB-B 250   | 0164114    | 26        | 46         | 84        | 52         |            | 99        | Stahl     | 7.2            |
|  | UVB-HS 250  | 0164120    | 26        |            | 115       | 86         | 48         | 99        | Stahl     | 5.25           |



Technische Beratung und Verkauf: Tel. +49-7133-103-2750