





Grundbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	m/Satz [kg]
	GBK 315	0159102	20	12	32		43	115		40	M12	3
	GBKL 315	0159122	20	12	32		43	137		40	M12	3.5
	GBK-V 315	0159152	20	12	32		43	115		40	M12	3
	STB-G 315-2	0160659	21		32	54	76	115			M16	7.5
	STNJ 315-5	0160652	18		32	50	54	120	15	30	M14	4.9
	STNJ 315-6	0160665	21		32	50	58	125	17.5	30	M16	5.5
	STN 315-6	0160603	21		32	45	56	110	13	28	M16	4.5



Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHF 250	0155102	12	20	30	55	50	90	14	40	M12	Stahl	1.9

Harte Stufenblockbacken



	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Werkstoff	m/Satz [kg]
	GST 315	0162102	32	66	32	116.3	10	Stahl	3.5

Segmentbacken




	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA-SM 250	0173102	12	20	180	70	250	60	55	45	90	44	40	M12	Stahl	12.8
	SFA-SM 251	0173106	12	20	180	70	250	80	75	65	90	44	40	M12	Stahl	16.8
	SFA-SA 250	0174102	12	20	180	70	250	58	53	43	87.5	44	40	M12	Aluminium	4.8
	SFA-SA 251	0174106	12	20	180	70	250	80	75	65	87.5	44	40	M12	Aluminium	6.4



Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA 250	0153102	12	20	30	55.5	50.5		125	35	40	M12	Stahl	3.7
	SFA 250-C1	0154101	12	20	40		60	55	90	26	40	M12	Stahl	3.9
	SFA 250-C2	0154102	12	20	40		60	55	125	26	40	M12	Stahl	5.6
	SFA 250-C3	0154103	12	20	40		80	75	125	26	40	M12	Stahl	7.7
	SFA 250-C4	0154104	12	20	40		100	95	125	26	40	M12	Stahl	9.8
	SFA 250-C5	0154105	12	20	40		120	115	125	26	40	M12	Stahl	11.8
	SFA 250-C6	0154106	12	20	60		60	55	90	26	40	M12	Stahl	6
	SFA 250-C7	0154107	12	20	80		60	55	90	26	40	M12	Stahl	8.5
	SFA 250-C8	0154134	12	20	80		100	95	125	26	40	M12	Stahl	20.9
	SFA-AL 250	0172103	12	20	40	60	55		125	35	40	M12	Aluminium	2.1

Weiche Blockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	B1 [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	Werkstoff	m/Satz [kg]
	UVB 315	0164102	32		90	56		121	Stahl	7.6
	UVB-H 315	0164118	32		135	101		121	Stahl	11.3
	UVB-B 315	0164115	32	46	90	52		121	Stahl	9.6
	UVB-HS 315	0164121	32		135	101	52	121	Stahl	9

