



SCHUNK chuck jaws for HG-2G 400-128


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	30 - 140	423	II	SZKA-ST 311	0182156	12	26	32	50	40	54	M12	Steel	2.2


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	98 - 229	422	I	SZKI 319	0166162	12	26	40	53	25	M8	54	M12	Steel	3.9
	195 - 338	422	I	SZKI 322	0166165	12	26	40	53	25	M8	54	M12	Steel	2.7
	97 - 152	422	II	SZKI 319	0166162	12	26	40	53	25	M8	54	M12	Steel	3.9
	128 - 260	422	II	SZKI 322	0166165	12	26	40	53	25	M8	54	M12	Steel	2.7

Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	90 - 232	423	I	SZKA 321	0139166	12	26	40	53	25	M8	54	M12	Steel	3.1
	198 - 341	431	I	SZKA 324	0139169	12	26	40	53	25	M8	54	M12	Steel	2.8
	48 - 155	423	II	SZKA 321	0139166	12	26	40	53	25	M8	54	M12	Steel	3.1
	131 - 263	423	II	SZKA 324	0139169	12	26	40	53	25	M8	54	M12	Steel	2.8

Pendulum jaws

	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	108 - 196	377	PNK-G 400-2	0190619	99	50	3.7
	180 - 279	473	PNK-G 400-4	0190621	99	50	4.8
	228 - 328	494	PNK-G 400-6	0190623	99	50	5.28



Technical advice and sales: Tel. +49-7133-103-2750