



SCHUNK chuck jaws for HG-2G 500-165


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	174 - 331	522	I	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Steel	6
	264 - 421	521	I	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Steel	5.5
	110 - 224	533	II	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Steel	6
	158 - 314	533	II	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Steel	5.5

Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	144 - 301	522	I	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Steel	6
	245 - 402	522	I	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Steel	5.1
	55 - 194	534	II	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Steel	6
	125 - 295	534	II	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Steel	5.1

Pendulum jaws

	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	108 - 195	463	PNK-G 500-2	0190625	118	50	4.4
	163 - 242	538	PNK-G 500-4	0190627	118	50	5.5
	215 - 277	471	PNK-G 500-6	0190629	118	50	5.8
	245 - 342	511	PNK-G 500-8	0190631	118	50	6.2
	307 - 468	651	PNK-G 500-10	0190633	118	50	8.3



Technical advice and sales: Tel. +49-7133-103-2750