




SCHUNK chuck jaws for SP 240


Full Grip Jaws

	Description	ID	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set
	SWB-SM 200	0169101	17	140	64	200	60	50	69.5	35	22	M12	Steel	8.6
	SWB-SM 201	0169106	17	140	64	200	75	65	69.5	35	22	M12	Steel	10.8
	SWB-SA 200	0170101	17	140	50	200	58	48	72.5	35	22	M12	Aluminum	3.4
	SWB-SA 201	0170106	17	140	50	200	75	65	72.5	35	22	M12	Aluminum	4.2

Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB 210	0121102	17	40	49	84.3	12	28.7	19	19	M12	Steel	2

Jaw blanks



	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Min. distance a (jaw tip up to first hole) [mm]	Min. distance b (first up to second hole) [mm]	Screws	Material	m/piece [kg]
	SBM 31	0112100	17	40	40	70	12	22	M12	Steel	0.9
	SBM 32	0112101	17	40	40	90	12	22	M12	Steel	1.1
	SBM 33	0112102	17	40	40	105	12	22	M12	Steel	1.2
	SBM 34	0112103	17	40	60	70	12	22	M12	Steel	1.3
	SBM 35	0112104	17	40	60	90	12	22	M12	Steel	1.7
	SBM 36	0112105	17	40	60	105	12	22	M12	Steel	2
	SBM 361	0112136	17	40	60	120	12	22	M12	Steel	2.2
	SBM 3610	0112107	17	40	100	90	12	22	M12	Steel	2.7
	SBM 3612	0112108	17	40	120	90	12	22	M12	Steel	3.4
	SBM 3615	0112139	17	50	80	90	12	22	M12	Steel	2.7
	SBM 368	0112106	17	40	80	90	12	22	M12	Steel	2.3
	SBM 37	0112109	17	60	60	70	12	22	M12	Steel	1.9
	SBM 38	0112110	17	60	60	90	12	22	M12	Steel	2.4
	SBM 40	0112111	17	80	60	90	12	22	M12	Steel	3.3





Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for SP 240

Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 170	0112170	17	40	60	420	Steel	7.6
	SBM-ST 171	0112171	17	40	80	420	Steel	10.2
	SBM-ST 172	0112172	17	40	100	420	Steel	12.8
	SBM-STA 170	0112173	17	40	60	420	Aluminum	2.8

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWBL 200	0120153	17	35	40	98	4	15	22	M12	Steel	2.6
	CWB 200	0100006	17	40	40	90		25	22	M12	Steel	2.7
	SWB 200	0120104	17	40	60	90		25	22	M12	Steel	4.1
	SWB-AL 200	0168101	17	40	60	90		25	22	M12	Aluminum	1.5

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NS 126	0143102	17	27	9	M12	M12 x 35	70



Technical advice and sales: Tel. +49-7133-103-2750