




SCHUNK chuck jaws for KFD 130



Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB 130	0121100	12	30	38	57	10	16	15	15	M8	Steel	0.7

Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 120	0112160	12	35	60	420	Steel	6.7
	SBM-ST 121	0112163	12	40	80	420	Steel	10.2
	SBM-STA 120	0112161	12	35	60	420	Aluminum	2.4

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB 130	0120100	12	30	38	55.5	10	16	M8	Steel	1.2
	SWB-AL 130	0168104	12	30	40	55	10	16	M8	Aluminum	0.45

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NS 80	0140100	12	17.2	7	M8	M8 x 22	30



Technical advice and sales: Tel. +49-7133-103-2750