




# SCHUNK chuck jaws for HG-F 500



## Base Jaws

|                                                                                   | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | B1<br>[mm] | H<br>[mm] | L<br>[mm] | b<br>[mm] | Screws  | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|------------|-----------|-----------|-----------|---------|---------------|
|  | SFG 400     | 0157104 | 30        | 18        | 45        |            | 51        | 160       | 60        | M16x1.5 | 7.2           |
|                                                                                   | SFGL 400    | 0157124 | 30        | 18        | 45        |            | 51        | 200       | 60        | M16x1.5 | 8.6           |
|  | STB 400-1   | 0156104 | 21        |           | 45        | 54         | 80        | 160       |           | M16     | 12            |
|                                                                                   | STB 400-2   | 0156105 | 25.5      |           | 45        | 64         | 82        | 160       |           | M20     | 12.2          |


## Claw jaws for O.D. clamping

|                                                                                   | Clamping<br>range ØD | Swing<br>diameter<br>SDmax | Position of<br>base jaws | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | G  | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|----------------------|----------------------------|--------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|----|-----------|--------|----------|---------------|
|  | 266 - 402            | 520                        | I                        | SZKA 412    | 0139173 | 18        | 30        | 50        | 71        | 33        | M8 | 60        | M16    | Steel    | 5.1           |
|                                                                                   | 66 - 166             | 504                        | II                       | SZKA 409    | 0139170 | 18        | 30        | 50        | 71        | 33        | M8 | 60        | M16    | Steel    | 6             |
|                                                                                   | 147 - 267            | 504                        | II                       | SZKA 412    | 0139173 | 18        | 30        | 50        | 71        | 33        | M8 | 60        | M16    | Steel    | 5.1           |


## Full Grip Jaws

|                                                                                     | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | B1<br>[mm] | Ø D<br>[mm] | H<br>[mm] | H1<br>[mm] | H2<br>[mm] | L<br>[mm] | L1<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|------------|-------------|-----------|------------|------------|-----------|------------|-----------|--------|----------|---------------|
|  | SFA-SM 400  | 0173104 | 18        | 30        | 330       | 150        | 440         | 85        | 78         | 55         | 160       | 95         | 60        | M16    | Steel    | 55.6          |
|  | SFA-SA 400  | 0174104 | 18        | 30        | 330       | 150        | 440         | 90        | 83         | 60         | 160       | 95         | 60        | M16    | Aluminum | 22.8          |

## Hard Stepped Block Jaws

|                                                                                     | Description | ID      | B<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | T<br>[mm] | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-----------|-----------|----------|---------------|
|  | STF 400     | 0161104 | 45        | 93        | 52         | 167       | 20        | Steel    | 10.8          |

## Hard Stepped Top Jaws


|                                                                                     | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | T<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|------------|-----------|-----------|-----------|--------|----------|---------------|
|  | SHF 400     | 0155104 | 18        | 30        | 45        | 82        | 75         | 130       | 20        | 60        | M16    | Steel    | 6.8           |





Technical advice and sales: Tel. +49-7133-103-2750

# SCHUNK chuck jaws for HG-F 500

## Soft Monoblock Jaws

|                                                                                   | Description | ID      | B<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-----------|----------|---------------|
|  | SMB 400     | 0163104 | 45        | 93        | 53         | 176       | Steel    | 15            |
|                                                                                   | SMB 500     | 0163105 | 45        | 130       | 90         | 176       | Steel    | 21.6          |

## Soft Top Jaws

|                                                                                   | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | H1<br>[mm] | H2<br>[mm] | L<br>[mm] | L1<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|------------|------------|-----------|------------|-----------|--------|----------|---------------|
|  | SFA 400     | 0153104 | 18        | 30        | 50        | 80        | 73         |            | 180       | 50         | 60        | M16    | Steel    | 13.5          |
|                                                                                   | SFA 400-C1  | 0154116 | 18        | 30        | 60        |           | 80         | 73         | 130       | 35         | 60        | M16    | Steel    | 11.8          |
|                                                                                   | SFA 400-C3  | 0154118 | 18        | 30        | 60        |           | 100        | 93         | 155       | 35         | 60        | M16    | Steel    | 21.5          |
|                                                                                   | SFA 400-C4  | 0154119 | 18        | 30        | 60        |           | 120        | 113        | 155       | 35         | 60        | M16    | Steel    | 22.4          |
|                                                                                   | SFA 400-C5  | 0154120 | 18        | 30        | 80        |           | 80         | 73         | 130       | 35         | 60        | M16    | Steel    | 16            |
|                                                                                   | SFA 400-C6  | 0154125 | 18        | 30        | 58        |           | 180        | 173        | 160       | 35         | 60        | M16    | Steel    | 35.1          |
|                                                                                   | SFA 400-C7  | 0154135 | 18        | 30        | 96        |           | 115        | 108        | 115       | 35         | 60        | M16    | Steel    | 25.9          |
|  | SFA-AL 400  | 0172105 | 18        | 30        | 50        | 80        | 73         |            | 180       | 50         | 60        | M16    | Aluminum | 5.1           |



Technical advice and sales: Tel. +49-7133-103-2750