



SCHUNK Spannbacken für HG-N 160


Grundbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Schrauben	m/Satz [kg]
	GBK 160	0159106	18	8	20	27.5	65	32	M8	0.6
	GBK-V 160	0159156	18	8	20	27.5	65	32	M8	0.6


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHF 160	0155100	8	18	20	36.5	32.5	63	7.5	32	M8	Stahl	0.6


Harte Stufenblockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Werkstoff	m/Satz [kg]
	GST 140-160 I	0162097	20	43.5	22	58	7	Stahl	0.7
	GST 140-160 II	0162098	20	43.5	22	58	7	Stahl	0.7


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	80 - 120	200	I	SZKA 163	0165146	8	18	40	40	20	M6	32	M8	Stahl	1
	32 - 72	193	I	SZKA 169	0165174	8	18	26	40	20	M6	32	M8	Stahl	1
	57 - 100	192	II	SZKA 163	0165146	8	18	40	40	20	M6	32	M8	Stahl	1
	112 - 156	213	II	SZKA 168	0165151	8	18	30	40	20	M6	32	M8	Stahl	1.3

Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	47 - 71	192	I	SZKI 167	0166150	8	18	35	40	20	M6	32	M8	Stahl	0.9
	91 - 131	192	I	SZKI 169	0166152	8	18	30	40	20	M6	32	M8	Stahl	1.3
	69 - 112	191	II	SZKI 169	0166152	8	18	30	40	20	M6	32	M8	Stahl	1.3

Krallenbacken für Stangenspannung



	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	10 - 43	192	II	SZKA-ST 161	0182150	8	18	22	40	30	32	M8	Stahl	0.8





Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für HG-N 160



QUENTES Kunststoffbacken

	Spannbereich ØD	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Max. Anzugsmo- ment [Nm]	Schrauben	m/Satz [kg]
	20 - 73	TRQK 160	0150024	8	18	38	54	56	32		M8	0.5
		QUENTES 10-3	0150100							8		


Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA-SM 160	0173100	8	18	120	40	160	50	46	40	60	23	32	M8	Stahl	4.8
	SFA-SA 160	0174100	8	18	120	40	165	50	46	40	59.5	23	32	M8	Aluminium	1.8

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA 160	0153100	8	18	20	40	36		85	25	32	M8	Stahl	1.2
	SFA 160-C1	0154121	8	18	30		55.5	51.5	85	19	32	M8	Stahl	2.7
	SFA 160-C2	0154127	8	18	35		40	36	63	19	32	M8	Stahl	1.6
	SFA 160-C3	0154131	8	18	40		60	56	70	19	32	M8	Stahl	3.3
	SFA 160-C4	0154133	8	18	40		80	76	85	19	32	M8	Stahl	5.6
	SFA-AL 160	0172100	8	18	25	50	46		85	25	32	M8	Aluminium	0.7

Weiche Blockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	Werkstoff	m/Satz [kg]
	UVB 160	0164106	20	55.5	35	65	Stahl	1.6



Technische Beratung und Verkauf: Tel. +49-7133-103-2750