


SCHUNK Spannbacken für IL-D 800



Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Min. Abstand a (Backen- spitze bis erste Bohrung) [mm]	Min. Abstand b (Erste bis zweite Bohrung) [mm]	Schrauben	Werkstoff	m/Stück [kg]
	SBM 50	0112126	25.5	60	60	140	20	35	M20	Stahl	4
	SBM 51	0112127	25.5	60	80	140	20	35	M20	Stahl	5
	SBM 52	0112128	25.5	60	100	140	20	35	M20	Stahl	6.5
	SBM 53	0112129	25.5	60	100	155	20	35	M20	Stahl	7.2
	SBM 531	0112138	25.5	60	100	195	20	35	M20	Stahl	9.1
	SBM 5312	0112130	25.5	60	120	155	20	35	M20	Stahl	8.7
	SBM 5315	0112131	25.5	58	160	155	20	35	M20	Stahl	11.5
	SBM 5320	0112132	25.5	58	200	155	20	35	M20	Stahl	14.2
	SBM 57	0112134	25.5	80	80	155	20	35	M20	Stahl	7.2
	SBM 58	0112135	25.5	100	100	155	20	35	M20	Stahl	11.6



Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB 400	0121107	25.5	60	75	140	18	53	31	31	M20	Stahl	8

Verzahnte Stangen


	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	SBM-ST 250	0112190	25.5	60	100	420	Stahl	19.2
	SBM-ST 251	0112191	25.5	58	160	420	Stahl	30.9
	SBM-STA 250	0112187	25.5	60	100	420	Aluminium	7

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	CWB 400	0100008	25.5	60	80	140	30	35	M20	Stahl	12.6
	SWB 400	0120107	25.5	60	90	155	30	35	M20	Stahl	16
	SWB-AL 400	0168103	25.5	60	100	155	30	35	M20	Aluminium	6.4

SCHUNK Spannbacken für IL-D 800

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	S1 [mm]	H [mm]	H1 [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmo- ment [Nm]
	NS 204	0142123	28	25.5	40	15.5	M20	M20 x 40	300



Technische Beratung und Verkauf: Tel. +49-7133-103-2750