



SCHUNK chuck jaws for KNCS 500


Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Screws	m/set [kg]
	GBK 500	0159104	30	18	45	57	160	60	M16	8.6



Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	269 - 422	521	I	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Steel	5.5
	103 - 210	519	II	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Steel	6
	156 - 300	519	II	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Steel	5.5


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	250 - 403	522	I	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Steel	5.1
	50 - 180	520	II	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Steel	6
	130 - 281	520	II	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Steel	5.1

Full Grip Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA-SM 400	0173104	18	30	330	150	440	85	78	55	160	95	60	M16	Steel	55.6
	SFA-SA 400	0174104	18	30	330	150	440	90	83	60	160	95	60	M16	Aluminum	22.8

Hard Stepped Block Jaws


	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Material	m/set [kg]
	GST 500-630	0162104	45	93	46	175	20	Steel	11.7




Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KNCS 500



Hard Stepped Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 400	0155104	18	30	45	82	75	130	20	60	M16	Steel	6.8

Soft Monoblock Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	Material	m/set [kg]
	UVB 500	0164104	45	124	77	175	Steel	20.3

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 400	0153104	18	30	50	80	73		180	50	60	M16	Steel	13.5
	SFA 400-C1	0154116	18	30	60		80	73	130	35	60	M16	Steel	11.8
	SFA 400-C3	0154118	18	30	60		100	93	155	35	60	M16	Steel	21.5
	SFA 400-C4	0154119	18	30	60		120	113	155	35	60	M16	Steel	22.4
	SFA 400-C5	0154120	18	30	80		80	73	130	35	60	M16	Steel	16
	SFA 400-C6	0154125	18	30	58		180	173	160	35	60	M16	Steel	35.1
	SFA 400-C7	0154135	18	30	96		115	108	115	35	60	M16	Steel	25.9
	SFA-AL 400	0172105	18	30	50	80	73		180	50	60	M16	Aluminum	5.1



Technical advice and sales: Tel. +49-7133-103-2750