



SCHUNK Spannbacken für KFD-HS 250


Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Min. Abstand a (Backen- spitze bis erste Bohrung) [mm]	Min. Abstand b (erste bis zweite Bohrung) [mm]	Schrauben	Werkstoff	m/Stück [kg]
	SBM 31	0112100	17	40	40	70	12	22	M12	Stahl	0.9
	SBM 32	0112101	17	40	40	90	12	22	M12	Stahl	1.1
	SBM 33	0112102	17	40	40	105	12	22	M12	Stahl	1.2
	SBM 34	0112103	17	40	60	70	12	22	M12	Stahl	1.3
	SBM 35	0112104	17	40	60	90	12	22	M12	Stahl	1.7
	SBM 36	0112105	17	40	60	105	12	22	M12	Stahl	2
	SBM 361	0112136	17	40	60	120	12	22	M12	Stahl	2.2
	SBM 3610	0112107	17	40	100	90	12	22	M12	Stahl	2.7
	SBM 3612	0112108	17	40	120	90	12	22	M12	Stahl	3.4
	SBM 3615	0112139	17	50	80	90	12	22	M12	Stahl	2.7
	SBM 368	0112106	17	40	80	90	12	22	M12	Stahl	2.3
	SBM 37	0112109	17	60	60	70	12	22	M12	Stahl	1.9
	SBM 38	0112110	17	60	60	90	12	22	M12	Stahl	2.4
	SBM 40	0112111	17	80	60	90	12	22	M12	Stahl	3.3


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB 210	0121102	17	40	49	84.3	12	28.7	19	19	M12	Stahl	2

Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	33 - 103	275	SZA 25-6	0138176	17	35	55	25	M6	22	M12	Stahl	2.3
	54 - 134	256	SZA 25-7	0138177	17	35	55	25	M6	22	M12	Stahl	1.7
	110 - 193	263	SZA 25-8	0138178	17	40	55	25	M6	22	M12	Stahl	1.8
	145 - 228	298	SZA 25-9	0138179	17	40	55	25	M6	22	M12	Stahl	2.4

Krallenbacken für Innenspannung


	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	59 - 136	274	SZI 25-17	0123180	17	35	55	25	M6	22	M12	Stahl	1.9
	79 - 161	260	SZI 25-18	0123181	17	40	55	25	M6	22	M12	Stahl	2.2
	142 - 225	270	SZI 25-19	0123182	17	40	55	25	M6	22	M12	Stahl	2




Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für KFD-HS 250



Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	18 - 84	271	SZA-ST 25-1	0175102	17	35	45	35	22	M12	Stahl	1.8


Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	61 - 87	219	PNS-Z 200-1	0190138	56	30	1.2
	63 - 120	254	PNS-Z 200-2	0190139	56	30	1.3
	92 - 147	274	PNS-Z 200-3	0190140	56	30	1.4
	122 - 177	273	PNS-Z 200-4	0190141	56	30	1.5
	47 - 92	257	PNS-Z 250-17-1	0190100	56	35	1.6
	63 - 109	269	PNS-Z 250-17-2	0190101	56	35	1.7
	85 - 107	269	PNS-Z 250-17-3	0190102	56	35	1.9
	106 - 161	283	PNS-Z 250-17-4	0190103	56	35	2.2
	115 - 170	283	PNS-Z 250-17-5	0190104	56	35	2.4

Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	FR-SM 200	0120702	17	140	50	200	60	50	70	36	19	M12	Stahl	8.4
	FR-SA 200	0120652	17	140	50	200	58	48	72.5	40	19	M12	Aluminium	3.4

Verzahnte Stangen



	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	SBM-ST 170	0112170	17	40	60	420	Stahl	7.6
	SBM-ST 171	0112171	17	40	80	420	Stahl	10.2
	SBM-ST 172	0112172	17	40	100	420	Stahl	12.8
	SBM-STA 170	0112173	17	40	60	420	Aluminium	2.8






Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für KFD-HS 250

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWB-FR 250	0120405	17	40	60	90	12	19	M12	Stahl	4.1
	FR-AL 200	0120602	17	40	60	90	12	19	M12	Aluminium	1.6

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	S1 [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdreh- moment [Nm]
	NS 163	0142102	21		25.5	11		M16	M16 x 35	150
	NS 122	0140107	21	17	25.5	11		M12	M12 x 30	70
	NK 162	0147110	21		25.5	11	25	M16	M16 x 30	150
	NK 161	0147109	21	17	25.5	11	19	M12	M12 x 30	70



Technische Beratung und Verkauf: Tel. +49-7133-103-2750