



SCHUNK Spannbacken für KNCS-2G 500-155


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	133 - 328	550	I	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Stahl	6
	234 - 430	550	I	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Stahl	5.1
	58 - 221	562	II	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Stahl	6
	128 - 323	562	II	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Stahl	5.1

Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	164 - 359	550	I	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Stahl	6
	253 - 449	549	I	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Stahl	5.5
	123 - 251	561	II	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Stahl	6
	160 - 342	561	II	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Stahl	5.5

Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	108 - 196	464	PNK-G 500-2	0190625	118	50	4.4
	163 - 267	567	PNK-G 500-4	0190627	118	50	5.5
	213 - 278	472	PNK-G 500-6	0190629	118	50	5.8
	243 - 343	512	PNK-G 500-8	0190631	118	50	6.2
	307 - 480	665	PNK-G 500-10	0190633	118	50	8.3



Technische Beratung und Verkauf: Tel. +49-7133-103-2750