



SCHUNK Spannbacken für KNCS-2G 210-52


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	39 - 91	259	I	SZKA 212	0139153	10	20	26	45	25	M6	40	M8	Stahl	1.4
	101 - 166	259	I	SZKA 213	0139154	10	20	30	45	25	M6	40	M8	Stahl	1.3
	136 - 201	265	I	SZKA 216	0139159	10	20	30	45	25	M6	40	M8	Stahl	1.2
	35 - 53	257	II	SZKA 212	0139153	10	20	26	45	25	M6	40	M8	Stahl	1.4
	72 - 128	257	II	SZKA 213	0139154	10	20	30	45	25	M6	40	M8	Stahl	1.3
	107 - 163	257	II	SZKA 216	0139159	10	20	30	45	25	M6	40	M8	Stahl	1.2


Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	59 - 105	258	I	SZKI 209	0166154	10	20	30	45	20	M6	40	M8	Stahl	1.7
	110 - 175	258	I	SZKI 211	0166156	10	20	30	45	20	M6	40	M8	Stahl	1.4
	58 - 67	256	II	SZKI 209	0166154	10	20	30	45	20	M6	40	M8	Stahl	1.7
	90 - 136	256	II	SZKI 211	0166156	10	20	30	45	20	M6	40	M8	Stahl	1.4


Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	24 - 79	257	II	SZKA-ST 201	0182152	10	20	22	45	37	40	M8	Stahl	0.9

Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	53 - 87	226	PNK-G 200-2	0190659	76	36	1.2
	86 - 131	257	PNK-G 200-6	0190663	76	36	1.6
	105 - 161	255	PNK-G 200-8	0190665	76	36	1.8

Weiche Blockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	Werkstoff	m/Satz [kg]
	UVB-HS 200	0164119	22	85	60	29	84	Stahl	2.67



Technische Beratung und Verkauf: Tel. +49-7133-103-2750