



SCHUNK chuck jaws for KNCS-2G 500-155


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	164 - 359	550	I	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Steel	6
	253 - 449	549	I	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Steel	5.5
	123 - 251	561	II	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Steel	6
	160 - 342	561	II	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Steel	5.5

Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	133 - 328	550	I	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Steel	6
	234 - 430	550	I	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Steel	5.1
	58 - 221	562	II	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Steel	6
	128 - 323	562	II	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Steel	5.1

Pendulum jaws

	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	108 - 196	464	PNK-G 500-2	0190625	118	50	4.4
	163 - 267	567	PNK-G 500-4	0190627	118	50	5.5
	213 - 278	472	PNK-G 500-6	0190629	118	50	5.8
	243 - 343	512	PNK-G 500-8	0190631	118	50	6.2
	307 - 480	665	PNK-G 500-10	0190633	118	50	8.3



Technical advice and sales: Tel. +49-7133-103-2750