



SCHUNK chuck jaws for KFG 215


Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	HSKN 215	0129101	14	36	52.5	81	12	25	21	21	M10	Steel	1.85

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	M [mm]	a1 [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SKN 215	0127103	14	35	60	89	34		18	26		M10	Steel	3.6
	SKNL 215	0128101	14	40	42	102	34	3	16	22	22	M10	Steel	2.9

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NSK 215	0144103	14	16.5	6.5	M10	M10 x 20	50



Technical advice and sales: Tel. +49-7133-103-2750