



SCHUNK chuck jaws for KNCS-2G 325-104


Base Jaws

	Description	ID	N [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	m/set [kg]
	STNJ 315-5	0160652	18	32	50	54	120	15	30	M14	4.9
	STNJ 315-6	0160665	21	32	50	58	125	17.5	30	M16	5.5


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	64 - 129	381	II	SZKA-ST 251	0182154	12	20	26	45	35	40	M12	Steel	1.2


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
				SZKI 261	0166158	12	20	40	50	25	M6	40	M12	Steel	2.8
	208 - 328	384	I	SZKI 264	0166161	12	20	40	50	25	M6	40	M12	Steel	2.2
	79 - 122	380	II	SZKI 261	0166158	12	20	40	50	25	M6	40	M12	Steel	2.8
	121 - 240	380	II	SZKI 264	0166161	12	20	40	50	25	M6	40	M12	Steel	2.2


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	113 - 233	387	I	SZKA 263	0139160	12	20	30	50	25	M6	40	M12	Steel	1.4
	171 - 291	387	I	SZKA 266	0139163	12	20	40	50	25	M6	40	M12	Steel	1.9
	204 - 325	401	I	SZKA 268	0139165	12	20	40	50	25	M6	40	M12	Steel	2.2
	39 - 146	381	II	SZKA 263	0139160	12	20	30	50	25	M6	40	M12	Steel	1.4
	84 - 203	381	II	SZKA 266	0139163	12	20	40	50	25	M6	40	M12	Steel	1.9
	128 - 237	381	II	SZKA 268	0139165	12	20	40	50	25	M6	40	M12	Steel	2.2

Hard Stepped Block Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Material	m/set [kg]
	GST 315	0162102	32	66	32	116.3	10	Steel	3.5

Pendulum jaws


	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	67 - 110	299	PNK-G 315-2	0190611	93	40	2.6
	97 - 167	348	PNK-G 315-4	0190613	93	40	2.8
	152 - 209	332	PNK-G 315-6	0190615	93	40	3.1
	163 - 258	378	PNK-G 315-8	0190617	93	40	4



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KNCS-2G 325-104

Soft Monoblock Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	Material	m/set [kg]
	UVB-HS 315	0164121	32	135	101	52	121	Steel	9



Technical advice and sales: Tel. +49-7133-103-2750