



SCHUNK chuck jaws for KNCS-2G 260-78


Base Jaws

	Description	ID	N [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	m/set [kg]
	STNJ 250-5	0160651	16	26	40	49	110	10	30	M12	2.9
	STN 250-6	0160601	21	26	45	52	110	13	28	M16	4


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	65 - 75	304	II	SZKA-ST 251	0182154	12	20	26	45	35	40	M12	Steel	1.2


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	78 - 131	305	I	SZKI 261	0166158	12	20	40	50	25	M6	40	M12	Steel	2.8
	185 - 250	307	I	SZKI 264	0166161	12	20	40	50	25	M6	40	M12	Steel	2.2
	122 - 187	303	II	SZKI 264	0166161	12	20	40	50	25	M6	40	M12	Steel	2.2


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	90 - 156	309	I	SZKA 263	0139160	12	20	30	50	25	M6	40	M12	Steel	1.4
	148 - 213	310	I	SZKA 266	0139163	12	20	40	50	25	M6	40	M12	Steel	1.9
	181 - 247	324	I	SZKA 268	0139165	12	20	40	50	25	M6	40	M12	Steel	2.2
	40 - 92	304	II	SZKA 263	0139160	12	20	30	50	25	M6	40	M12	Steel	1.4
	85 - 150	304	II	SZKA 266	0139163	12	20	40	50	25	M6	40	M12	Steel	1.9
	129 - 183	304	II	SZKA 268	0139165	12	20	40	50	25	M6	40	M12	Steel	2.2

Pendulum jaws

	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	57 - 91	274	PNK-G 250-2	0190601	86	40	1.8
	85 - 109	290	PNK-G 250-6	0190605	86	40	2.2
	119 - 176	300	PNK-G 250-8	0190607	86	40	2.4
	128 - 185	300	PNK-G 250-10	0190609	86	40	2.5

Soft Monoblock Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	Material	m/set [kg]
	UVB-HS 250	0164120	26	115	86	48	99	Steel	5.25



Technical advice and sales: Tel. +49-7133-103-2750