



SCHUNK chuck jaws for KNCS-2G 210-52


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	24 - 79	257	II	SZKA-ST 201	0182152	10	20	22	45	37	40	M8	Steel	0.9


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	59 - 105	258	I	SZKI 209	0166154	10	20	30	45	20	M6	40	M8	Steel	1.7
	110 - 175	258	I	SZKI 211	0166156	10	20	30	45	20	M6	40	M8	Steel	1.4
	58 - 67	256	II	SZKI 209	0166154	10	20	30	45	20	M6	40	M8	Steel	1.7
	90 - 136	256	II	SZKI 211	0166156	10	20	30	45	20	M6	40	M8	Steel	1.4


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	39 - 91	259	I	SZKA 212	0139153	10	20	26	45	25	M6	40	M8	Steel	1.4
	101 - 166	259	I	SZKA 213	0139154	10	20	30	45	25	M6	40	M8	Steel	1.3
	136 - 201	265	I	SZKA 216	0139159	10	20	30	45	25	M6	40	M8	Steel	1.2
	35 - 53	257	II	SZKA 212	0139153	10	20	26	45	25	M6	40	M8	Steel	1.4
	72 - 128	257	II	SZKA 213	0139154	10	20	30	45	25	M6	40	M8	Steel	1.3
	107 - 163	257	II	SZKA 216	0139159	10	20	30	45	25	M6	40	M8	Steel	1.2

Pendulum jaws

	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	53 - 87	226	PNK-G 200-2	0190659	76	36	1.2
	86 - 131	257	PNK-G 200-6	0190663	76	36	1.6
	105 - 161	255	PNK-G 200-8	0190665	76	36	1.8

Soft Monoblock Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	Material	m/set [kg]
	UVB-HS 200	0164119	22	85	60	29	84	Steel	2.67



Technical advice and sales: Tel. +49-7133-103-2750