



SCHUNK chuck jaws for LP 500



Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SP-HB 400-500	0125105	25.5	57	73	160	22	43.1	42	42	M18	Steel	10.2


Jaw blanks

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Min. distance a (jaw tip up to first hole) [mm]	Min. distance b (first up to second hole) [mm]	Screws	Material	m/piece [kg]
	SBM 50	0112126	25.5	60	60	140	20	35	M20	Steel	4
	SBM 51	0112127	25.5	60	80	140	20	35	M20	Steel	5
	SBM 52	0112128	25.5	60	100	140	20	35	M20	Steel	6.5
	SBM 53	0112129	25.5	60	100	155	20	35	M20	Steel	7.2
	SBM 531	0112138	25.5	60	100	195	20	35	M20	Steel	9.1
	SBM 5312	0112130	25.5	60	120	155	20	35	M20	Steel	8.7
	SBM 5315	0112131	25.5	58	160	155	20	35	M20	Steel	11.5
	SBM 5320	0112132	25.5	58	200	155	20	35	M20	Steel	14.2
	SBM 57	0112134	25.5	80	80	155	20	35	M20	Steel	7.2
	SBM 58	0112135	25.5	100	100	155	20	35	M20	Steel	11.6

Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 250	0112190	25.5	60	100	420	Steel	19.2
	SBM-ST 251	0112191	25.5	58	160	420	Steel	30.9
	SBM-STA 250	0112187	25.5	60	100	420	Aluminum	7

Soft Top Jaws


	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SP-WB 500	0124106	25.5	60	100	195	37	40	M18	Steel	24.8



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for LP 500

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NS 181	0143105	25.5	34.5	14.5	M18	M18 x 55	220



Technical advice and sales: Tel. +49-7133-103-2750