


SCHUNK Spannbacken für NTL-D 260


Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Min. Abstand a (Backen- spitze bis erste Bohrung) [mm]	Min. Abstand b (erste bis zweite Bohrung) [mm]	Schrauben	Werkstoff	m/Stück [kg]
	SBM 31	0112100	17	40	40	70	12	22	M12	Stahl	0.9
	SBM 32	0112101	17	40	40	90	12	22	M12	Stahl	1.1
	SBM 33	0112102	17	40	40	105	12	22	M12	Stahl	1.2
	SBM 34	0112103	17	40	60	70	12	22	M12	Stahl	1.3
	SBM 35	0112104	17	40	60	90	12	22	M12	Stahl	1.7
	SBM 36	0112105	17	40	60	105	12	22	M12	Stahl	2
	SBM 361	0112136	17	40	60	120	12	22	M12	Stahl	2.2
	SBM 3610	0112107	17	40	100	90	12	22	M12	Stahl	2.7
	SBM 3612	0112108	17	40	120	90	12	22	M12	Stahl	3.4
	SBM 3615	0112139	17	50	80	90	12	22	M12	Stahl	2.7
	SBM 368	0112106	17	40	80	90	12	22	M12	Stahl	2.3
	SBM 37	0112109	17	60	60	70	12	22	M12	Stahl	1.9
	SBM 38	0112110	17	60	60	90	12	22	M12	Stahl	2.4
	SBM 40	0112111	17	80	60	90	12	22	M12	Stahl	3.3

Harte Stufenaufsatzbacken


	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB 175	0121103	17	35	44	64.7	10	28	19		M12	Stahl	1.2
	SHB 200	0121104	17	40	49	72.5	12	18	19	19	M12	Stahl	1.6
	SHB 210	0121102	17	40	49	84.3	12	28.7	19	19	M12	Stahl	2

Krallenbacken für Außenspannung


	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	67 - 159	275	SZA 16-30	0122110	17	35	50	20	M5	19	M12	Stahl	1.3
	86 - 178	278	SZA 16-31	0122111	17	35	50	20	M5	19	M12	Stahl	1.2
	108 - 200	278	SZA 16-32	0122112	17	35	50	20	M5	19	M12	Stahl	1.1
	127 - 219	279	SZA 16-33	0122113	17	40	50	20	M5	19	M12	Stahl	1.2
	149 - 241	301	SZA 16-34	0122114	17	40	50	20	M5	19	M12	Stahl	1.6
	40 - 125	278	SZA 20-14	0138195	17	35	50	25	M6	22	M12	Stahl	1.8
	67 - 152	278	SZA 20-15	0138196	17	35	50	25	M6	22	M12	Stahl	1.5
	97 - 182	279	SZA 20-16	0138197	17	40	50	25	M6	22	M12	Stahl	1.5
	124 - 209	280	SZA 20-17	0138198	17	40	50	25	M6	22	M12	Stahl	1.6
	240 - 303	154	SZA 20-18	0138199	17	40	50	25	M6	22	M12	Stahl	1.8
	36 - 120	294	SZA 25-6	0138176	17	35	55	25	M6	22	M12	Stahl	2.3
	66 - 151	278	SZA 25-7	0138177	17	35	55	25	M6	22	M12	Stahl	1.7
	124 - 210	282	SZA 25-8	0138178	17	40	55	25	M6	22	M12	Stahl	1.8
	159 - 245	312	SZA 25-9	0138179	17	40	55	25	M6	22	M12	Stahl	2.4

SCHUNK Spannbacken für NTL-D 260


Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	84 - 176	275	SZI 16-18	0123190	17	35	50	20	M6	19	M12	Stahl	1.3
	97 - 187	274	SZI 16-19	0123191	17	40	50	20	M6	19	M12	Stahl	1.6
	117 - 208	276	SZI 16-20	0123192	17	40	50	20	M6	19	M12	Stahl	1.5
	138 - 229	278	SZI 16-21	0123193	17	40	50	20	M6	19	M12	Stahl	1.5
	75 - 160	278	SZI 20-10	0123164	17	35	50	20	M6	22	M12	Stahl	1.6
	103 - 189	280	SZI 20-11	0123165	17	40	50	20	M6	22	M12	Stahl	2
	135 - 220	279	SZI 20-12	0123166	17	40	50	20	M6	22	M12	Stahl	1.7
	69 - 154	294	SZI 25-17	0123180	17	35	55	25	M6	22	M12	Stahl	1.9
	94 - 179	279	SZI 25-18	0123181	17	40	55	25	M6	22	M12	Stahl	2.2
	157 - 243	293	SZI 25-19	0123182	17	40	55	25	M6	22	M12	Stahl	2



Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	46 - 138	279	SZA-ST 16-1	0175100	17	35	40	30	19	M12	Stahl	1.2
	26 - 112	275	SZA-ST 20-1	0175101	17	35	45	35	22	M12	Stahl	1.5
	17 - 101	289	SZA-ST 25-1	0175102	17	35	45	35	22	M12	Stahl	1.8

Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	78 - 118	252	PNS-Z 200-2	0190139	56	30	1.3
	107 - 145	273	PNS-Z 200-3	0190140	56	30	1.4
	137 - 175	271	PNS-Z 200-4	0190141	56	30	1.5
	63 - 90	256	PNS-Z 250-17-1	0190100	56	35	1.6
	69 - 114	275	PNS-Z 250-17-2	0190101	56	35	1.7
	85 - 126	284	PNS-Z 250-17-3	0190102	56	35	1.9
	121 - 174	298	PNS-Z 250-17-4	0190103	56	35	2.2
	130 - 183	298	PNS-Z 250-17-5	0190104	56	35	2.4

Segmentbacken



	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWB-SM 200	0169101	17	140	64	200	60	50	69.5	35	22	M12	Stahl	8.6
	SWB-SM 201	0169106	17	140	64	200	75	65	69.5	35	22	M12	Stahl	10.8
	SWB-SA 200	0170101	17	140	50	200	58	48	72.5	35	22	M12	Aluminium	3.4
	SWB-SA 201	0170106	17	140	50	200	75	65	72.5	35	22	M12	Aluminium	4.2

SCHUNK Spannbacken für NTL-D 260

Verzahnte Stangen

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	SBM-ST 170	0112170	17	40	60	420	Stahl	7.6
	SBM-ST 171	0112171	17	40	80	420	Stahl	10.2
	SBM-ST 172	0112172	17	40	100	420	Stahl	12.8
	SBM-STA 170	0112173	17	40	60	420	Aluminium	2.8

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWBL 200	0120153	17	35	40	98	4	15	22	M12	Stahl	2.6
	CWB 200	0100006	17	40	40	90		25	22	M12	Stahl	2.7
	SWB 200	0120104	17	40	60	90		25	22	M12	Stahl	4.1
	SWB-AL 200	0168101	17	40	60	90		25	22	M12	Aluminium	1.5



Technische Beratung und Verkauf: Tel. +49-7133-103-2750