




## Backenrohlinge

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Min. Abstand<br>a (Backen-<br>spitze bis<br>erste<br>Bohrung)<br>[mm] | Min. Abstand<br>b (erste bis<br>zweite<br>Bohrung)<br>[mm] | Schrauben | Werkstoff | m/Stück<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------------------------------------------------------------------|------------------------------------------------------------|-----------|-----------|-----------------|
|  | SBM 41      | 0112112    | 21        | 50        | 60        | 90        | 15                                                                    | 28                                                         | M16       | Stahl     | 2.1             |
|                                                                                   | SBM 42      | 0112113    | 21        | 50        | 60        | 105       | 15                                                                    | 28                                                         | M16       | Stahl     | 2.4             |
|                                                                                   | SBM 4210    | 0112115    | 21        | 50        | 100       | 120       | 15                                                                    | 28                                                         | M16       | Stahl     | 5               |
|                                                                                   | SBM 4212    | 0112116    | 21        | 50        | 120       | 120       | 15                                                                    | 28                                                         | M16       | Stahl     | 5.6             |
|                                                                                   | SBM 4215    | 0112117    | 21        | 50        | 150       | 120       | 15                                                                    | 28                                                         | M16       | Stahl     | 7               |
|                                                                                   | SBM 428     | 0112114    | 21        | 50        | 80        | 120       | 15                                                                    | 28                                                         | M16       | Stahl     | 3.7             |
|                                                                                   | SBM 4281    | 0112137    | 21        | 50        | 80        | 150       | 15                                                                    | 28                                                         | M16       | Stahl     | 4.6             |
|                                                                                   | SBM 43      | 0112118    | 21        | 60        | 60        | 90        | 15                                                                    | 28                                                         | M16       | Stahl     | 2.4             |
|                                                                                   | SBM 44      | 0112119    | 21        | 60        | 60        | 105       | 15                                                                    | 28                                                         | M16       | Stahl     | 2.9             |
|                                                                                   | SBM 45      | 0112120    | 21        | 60        | 80        | 90        | 15                                                                    | 28                                                         | M16       | Stahl     | 3.2             |
|                                                                                   | SBM 46      | 0112121    | 21        | 60        | 80        | 105       | 15                                                                    | 28                                                         | M16       | Stahl     | 3.8             |
|                                                                                   | SBM 47      | 0112122    | 21        | 60        | 80        | 120       | 15                                                                    | 28                                                         | M16       | Stahl     | 4.4             |
|                                                                                   | SBM 48      | 0112123    | 21        | 80        | 60        | 90        | 15                                                                    | 28                                                         | M16       | Stahl     | 3.2             |
|                                                                                   | SBM 498     | 0112125    | 21        | 80        | 80        | 120       | 15                                                                    | 28                                                         | M16       | Stahl     | 5.8             |

## Harte Stufenaufsatzbacken


|                                                                                     | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SHB 315     | 0121111    | 21        | 50        | 58        | 128       | 14        | 46        | 30        | 30        | M16       | Stahl     | 4.6            |

## Krallenbacken für Außenspannung


|                                                                                     | Spannbereich<br>ØD | Schwingkreis<br>SDmax | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | G  | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|--------------------|-----------------------|-------------|------------|-----------|-----------|-----------|-----------|----|-----------|-----------|-----------|----------------|
|  | 54 - 162           | 335                   | SZA 25-37   | 0138180    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 3.3            |
|                                                                                     | 93 - 202           | 335                   | SZA 25-38   | 0138181    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 2.9            |
|                                                                                     | 143 - 252          | 338                   | SZA 25-39   | 0138182    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 2.7            |
|                                                                                     | 189 - 299          | 374                   | SZA 25-40   | 0138183    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 3.2            |
|                                                                                     | 46 - 140           | 345                   | SZA 31-10   | 0138184    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 3.4            |
|                                                                                     | 89 - 197           | 346                   | SZA 31-11   | 0138185    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 3.4            |
|                                                                                     | 154 - 263          | 344                   | SZA 31-12   | 0138186    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 3.2            |
|                                                                                     | 217 - 327          | 404                   | SZA 31-13   | 0138187    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 4.5            |
|                                                                                     |                    |                       | SZA 40-11   | 0138300    | 25.5      | 60        | 78        | 33        | M8 | 35        | M20       | Stahl     | 8              |
|                                                                                     |                    |                       | SZA 40-12   | 0138301    | 25.5      | 60        | 78        | 33        | M8 | 35        | M20       | Stahl     | 11.5           |
|                                                                                     |                    |                       | SZA 40-13   | 0138302    | 25.5      | 60        | 78        | 33        | M8 | 35        | M20       | Stahl     | 8              |
|                                                                                     |                    |                       | SZA 40-14   | 0138303    | 25.5      | 60        | 78        | 33        | M8 | 35        | M20       | Stahl     | 8              |
|                                                                                     |                    |                       | SZA 40-15   | 0138304    | 25.5      | 60        | 78        | 33        | M8 | 35        | M20       | Stahl     | 9.3            |
|                                                                                     |                    |                       | SZA 40-16   | 0138305    | 25.5      | 60        | 78        | 33        | M8 | 35        | M20       | Stahl     | 11             |

# SCHUNK Spannbacken für NTL-D 315


## Krallenbacken für Innenspannung

|                                                                                   | Spannbereich<br>ØD | Schwingkreis<br>SDmax | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | G  | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|--------------------|-----------------------|-------------|------------|-----------|-----------|-----------|-----------|----|-----------|-----------|-----------|----------------|
|  | 83 - 190           | 342                   | SZI 25-34   | 0123183    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 3.5            |
|                                                                                   | 124 - 232          | 345                   | SZI 25-35   | 0123184    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 3.2            |
|                                                                                   | 169 - 277          | 344                   | SZI 25-36   | 0123185    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 3              |
|                                                                                   | 80 - 161           | 351                   | SZI 31-11   | 0123186    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 4.1            |
|                                                                                   | 127 - 215          | 344                   | SZI 31-12   | 0123187    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 4.2            |
|                                                                                   | 179 - 289          | 343                   | SZI 31-13   | 0123188    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 3.9            |



## Krallenbacken für Stangenspannung

|                                                                                   | Spannbereich<br>ØD | Schwingkreis<br>SDmax | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|--------------------|-----------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | 24 - 132           | 337                   | SZA-ST 25-2 | 0175103    | 21        | 45        | 50        | 40        | 28        | M16       | Stahl     | 2.7            |
|                                                                                   | 20 - 101           | 344                   | SZA-ST 31-1 | 0175104    | 21        | 45        | 50        | 40        | 28        | M16       | Stahl     | 3.3            |
|                                                                                   |                    |                       | SZA-ST 40-1 | 0175105    | 25.5      | 60        | 55        | 45        | 35        | M20       | Stahl     | 8              |

## Pendelbacken

|                                                                                     | Spannbereich<br>ØD | Schwingkreis<br>SDmax | Bezeichnung    | Ident.-Nr. | H<br>[mm] | T<br>[mm] | m/Stück<br>[kg] |
|-------------------------------------------------------------------------------------|--------------------|-----------------------|----------------|------------|-----------|-----------|-----------------|
|  | 84 - 113           | 274                   | PNS-Z 250-21-2 | 0190106    | 64        | 35        | 2               |
|                                                                                     | 88 - 134           | 294                   | PNS-Z 250-21-3 | 0190107    | 64        | 35        | 2.1             |
|                                                                                     | 140 - 178          | 303                   | PNS-Z 250-21-4 | 0190108    | 64        | 35        | 2.3             |
|                                                                                     | 149 - 198          | 315                   | PNS-Z 250-21-5 | 0190109    | 64        | 35        | 2.3             |
|                                                                                     | 68 - 108           | 287                   | PNS-Z 315-1    | 0190110    | 64        | 35        | 2               |
|                                                                                     | 97 - 159           | 330                   | PNS-Z 315-2    | 0190111    | 64        | 35        | 2.3             |
|                                                                                     | 145 - 207          | 330                   | PNS-Z 315-3    | 0190112    | 64        | 35        | 2.5             |
|                                                                                     | 163 - 232          | 349                   | PNS-Z 315-4    | 0190113    | 64        | 35        | 2.7             |
|                                                                                     | 201 - 232          | 351                   | PNS-Z 315-5    | 0190114    | 64        | 35        | 3.2             |

## Segmentbacken



|                                                                                     | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | B1<br>[mm] | Ø D<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|------------|-------------|-----------|------------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SWB-SM 315  | 0169104    | 21        | 240       | 120        | 320         | 70        | 55         | 110       | 60        | 28        | M16       | Stahl     | 26.6           |
|  | SWB-SA 315  | 0170104    | 21        | 240       | 80         | 320         | 78        | 63         | 117       | 70        | 28        | M16       | Aluminium | 12             |






Technische Beratung und Verkauf: Tel. +49-7133-103-2750

# SCHUNK Spannbacken für NTL-D 315

## Verzahnte Stangen

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Werkstoff | m/Stück<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------------|
|  | SBM-ST 210  | 0112180    | 21        | 50        | 60        | 420       | Stahl     | 9.4             |
|                                                                                   | SBM-ST 211  | 0112181    | 21        | 50        | 80        | 420       | Stahl     | 12.7            |
|                                                                                   | SBM-ST 212  | 0112182    | 21        | 50        | 120       | 420       | Stahl     | 19.3            |
|                                                                                   | SBM-ST 213  | 0112183    | 21        | 80        | 80        | 420       | Stahl     | 20.4            |
|  | SBM-STA 210 | 0112184    | 21        | 50        | 80        | 420       | Aluminium | 4.6             |

## Weiche Aufsatzbacken

|                                                                                     | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a1<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|------------|-----------|-----------|-----------|-----------|----------------|
|    | SWBL 250-21 | 0120155    | 21        | 50        | 50        | 120       | 4          | 20        | 28        | M16       | Stahl     | 5.6            |
|                                                                                     | SWBL 315    | 0120156    | 21        | 50        | 50        | 140       | 4          | 30        | 28        | M16       | Stahl     | 6.5            |
|   | CWB 251     | 0100012    | 21        | 50        | 60        | 95        |            | 15        | 28        | M16       | Stahl     | 5.2            |
|                                                                                     | SWB 250     | 0120105    | 21        | 50        | 80        | 120       |            | 30        | 28        | M16       | Stahl     | 9.4            |
|  | SWB-AL 250  | 0168102    | 21        | 50        | 80        | 120       |            | 30        | 28        | M16       | Aluminium | 3              |



Technische Beratung und Verkauf: Tel. +49-7133-103-2750