


SCHUNK chuck jaws for LVE 160



Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	12 - 53	194	SZA-ST 16-4	0175112	12	32	40	30	15	M8	Steel	1.1


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	33 - 83	191	SZA 16-10	0122250	12	32	40	20	M5	15	M8	Steel	1
	61 - 112	189	SZA 16-11	0122251	12	32	40	20	M5	15	M8	Steel	1
	81 - 132	190	SZA 16-12	0122252	12	32	40	20	M5	15	M8	Steel	0.9



Full Grip Jaws

	Description	ID	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	FR-SM 160	0120701	12	120	40	160	60	50	60	20	15	15	M8	Steel	6
	FR-SA 160	0120651	12	120	40	165	58	48	59.5	18	15	15	M8	Aluminum	2.1

Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB 130	0121100	12	30	38	57	10	16	15	15	M8	Steel	0.7

QUENTES fiberglass jaws

	Clamping range ØD	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Max. tightening torque [Nm]	Screws	m/set [kg]
	60 - 135	TRQ 200-2	0150002	17	40	64	79	19		M12	0.93
		QUENTES 20-3	0150200					8			






Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for LVE 160

Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 120	0112160	12	35	60	420	Steel	6.7
	SBM-ST 121	0112163	12	40	80	420	Steel	10.2
	SBM-STA 120	0112161	12	35	60	420	Aluminum	2.4

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB-FR 162	0120409	12	35	40	72	3	12	15	M8	Steel	1.6
	SWB 130	0120100	12	30	38	55.5		10	16	M8	Steel	1.2
	SWB-FR 160	0120402	12	30	38	55.5		9	15	M8	Steel	1.2
	SWB-FR 161	0120403	12	30	55.5	55		9	15	M8	Steel	1.8
	FR-AL 160	0120601	12	30	55	70		9	15	M8	Aluminum	0.9
	SWB-AL 130	0168104	12	30	40	55		10	16	M8	Aluminum	0.45

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NS 80	0140100	12	17.2	7	M8	M8 x 22	30



Technical advice and sales: Tel. +49-7133-103-2750