



SCHUNK Spannbacken für SP 125



Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB 125	0125100	11	26	40	58.5	9	14.5	16	16	M8	Stahl	0.7
	SHB 130	0121100	12	30	38	57	10	16	15	15	M8	Stahl	0.7

Verzahnte Stangen

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	SBM-ST 120	0112160	12	35	60	420	Stahl	6.7
	SBM-ST 121	0112163	12	40	80	420	Stahl	10.2
	SBM-STA 120	0112161	12	35	60	420	Aluminium	2.4

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SP-WB 125	0124100	11	30	40	55.5	10	18	M8	Stahl	1.3
	SWB 130	0120100	12	30	38	55.5	10	16	M8	Stahl	1.2
	SWB-AL 130	0168104	12	30	40	55	10	16	M8	Aluminium	0.45

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmoment [Nm]
	NS 81	0143100	11	21	7	M8	M8 x 30	30



Technische Beratung und Verkauf: Tel. +49-7133-103-2750