




SCHUNK Spannbacken für SP 160



Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB 165	0121101	14	30	46	79.7	11	16.6	22	22	M10	Stahl	1.3




Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWB-SM 165	0169099	14	120	40	160	60	50	59.5	25	20	M10	Stahl	5.6
	SWB-SA 165	0170099	14	120	40	165	58	48	59.5	25	20	M10	Aluminium	1.9

Verzahnte Stangen

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	SBM-ST 140	0112165	14	35	60	420	Stahl	6.6
	SBM-STA 140	0112166	14	35	60	420	Aluminium	2.4

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWBL 165	0120152	14	35	40	80	4	15	20	M10	Stahl	2.1
	SWB 165	0120101	14	35	60	68		15	20	M10	Stahl	2.5
	SWB-AL 165	0168105	14	35	60	80		15	20	M10	Aluminium	1.2



Technische Beratung und Verkauf: Tel. +49-7133-103-2750

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmoment [Nm]
	NS 102	0143101	14	25.5	8.5	M10	M10 x 35	50

