




SCHUNK chuck jaws for KFD 140


Full Grip Jaws

	Description	ID	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	FR-SM 130	0120700	10	100	35	130	40	35	50	15	12	12	M6	Steel	3
	FR-SA 130	0120650	10	100	35	130	48	43	47.4	15	12	12	M6	Aluminum	1.3




Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB-FR 130	0121109	10	26	37.5	58	10	11.6	12	12	M6	Steel	0.4

Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 100	0112150	10	35	60	420	Steel	6.7

Soft Top Jaws


	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SWB-FR 130	0120400	10	25	30	55.5	3	11	12	12	M6	Steel	0.8
	SWB-FR 133	0120410	10	32	32	62	2	9	12	12	M6	Steel	1.2
	SWB-FR 132	0132141	10	22	47	53		9	12	12	M6	Steel	1
	FR-AL 130	0120600	10	25	45	53	3	9	12	12	M6	Aluminum	0.4



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KFD 140

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NK 60	0147104	10	13.7	5.5	12	M6	M6 x 18	16



Technical advice and sales: Tel. +49-7133-103-2750