



SCHUNK Spannbacken für KFD-HE 315-91


Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Stück [kg]
	JBM 120	0114420	21	50	60	130	15	30	M16	Stahl	3.1
	JBM 121	0114421	21	50	80	130	15	30	M16	Stahl	4.1
	JBM 122	0114422	21	50	120	130	15	30	M16	Stahl	6
	JBM 123	0114423	21	58	150	130	15	30	M16	Stahl	8.8
	JBM 124	0114424	21	80	80	130	15	30	M16	Stahl	6.2


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB-J 126	0133105	21	50	62	128	14	46	30	30	M16	Stahl	5.15
	SHB-J 122	0133113	21	50	52	104	18	20	30	30	M16	Stahl	3.3


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
			SZAJ 30-5	0138131	21	50	65	25	M8	30	M16	Stahl	3.8
	100 - 191	357	SZAJ 30-6	0138132	21	50	65	25	M8	30	M16	Stahl	4.1
	166 - 258	348	SZAJ 30-7	0138133	21	50	65	25	M8	30	M16	Stahl	3.4
	229 - 315	384	SZAJ 30-8	0138134	21	50	65	25	M8	30	M16	Stahl	4.8

Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	78 - 163	340	SZIJ 30-13	0179128	21	50	65	25	M8	30	M16	Stahl	4.7
	129 - 225	347	SZIJ 30-14	0179129	21	50	65	25	M8	30	M16	Stahl	4.4
	193 - 289	330	SZIJ 30-15	0179130	21	50	65	25	M8	30	M16	Stahl	3.4
	245 - 341	382	SZIJ 30-16	0179131	21	50	65	25	M8	30	M16	Stahl	4.2

Krallenbacken für Stangenspannung



	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	24 - 104	327	SZAJ-ST 30-3	0175512	21	50	50	43	30	M16	Stahl	3.4




Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für KFD-HE 315-91




Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	KMWB-SM 301	0132704	21	240	120	300	70	55	110	45	30	M16	Stahl	26.4
	KMWB-SA 301	0132804	21	240	80	320	78	63	117	45	30	M16	Aluminium	10.9


Verzahnte Stangen

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	JBM-ST 210	0114540	21	50	80	420	Stahl	12.7
	JBM-ST 211	0114541	21	60	120	420	Stahl	23.2
	JBM-STA 210	0114542	21	50	80	420	Aluminium	4.6

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	KM-WBL 121	0132604	21	50	50	145	10	30	30	M16	Stahl	6.9
	KM-WB 126	0132131	21	50	60	129		39	30	M16	Stahl	7.8
	KM-WB 128	0132154	21	50	80	129		39	30	M16	Stahl	10.4
	KM-WBAL 121	0132525	21	50	80	130		40	30	M16	Aluminium	3.8

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmoment [Nm]
	NJ 124	0146123	21	28	11.5	30	M16	M16 x 40	150



Technische Beratung und Verkauf: Tel. +49-7133-103-2750