



SCHUNK chuck jaws for KFD-HS 110


Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 100	0112150	10	35	60	420	Steel	6.7

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB-FR 110	0120408	10	25	32	45	5	12	15	M8	Steel	0.6

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NK 40	0147112	10	15.7	6.5	15	M8	M8 x 20	30



Technical advice and sales: Tel. +49-7133-103-2750