




Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Stück [kg]
	SBM 31	0112100	17	40	40	70	12	22	M12	Stahl	0.9
	SBM 32	0112101	17	40	40	90	12	22	M12	Stahl	1.1
	SBM 33	0112102	17	40	40	105	12	22	M12	Stahl	1.2
	SBM 34	0112103	17	40	60	70	12	22	M12	Stahl	1.3
	SBM 35	0112104	17	40	60	90	12	22	M12	Stahl	1.7
	SBM 36	0112105	17	40	60	105	12	22	M12	Stahl	2
	SBM 361	0112136	17	40	60	120	12	22	M12	Stahl	2.2
	SBM 3610	0112107	17	40	100	90	12	22	M12	Stahl	2.7
	SBM 3612	0112108	17	40	120	90	12	22	M12	Stahl	3.4
	SBM 3615	0112139	17	50	80	90	12	22	M12	Stahl	2.7
	SBM 368	0112106	17	40	80	90	12	22	M12	Stahl	2.3
	SBM 37	0112109	17	60	60	70	12	22	M12	Stahl	1.9
	SBM 38	0112110	17	60	60	90	12	22	M12	Stahl	2.4
	SBM 40	0112111	17	80	60	90	12	22	M12	Stahl	3.3


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB 210	0121102	17	40	49	84.3	12	28.7	19	19	M12	Stahl	2


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	29 - 60	208	SZA 20-14	0138195	17	35	50	25	M6	22	M12	Stahl	1.8
	47 - 88	208	SZA 20-15	0138196	17	35	50	25	M6	22	M12	Stahl	1.5
	76 - 117	208	SZA 20-16	0138197	17	40	50	25	M6	22	M12	Stahl	1.5
	103 - 144	210	SZA 20-17	0138198	17	40	50	25	M6	22	M12	Stahl	1.6
	133 - 174	234	SZA 20-18	0138199	17	40	50	25	M6	22	M12	Stahl	1.8

Krallenbacken für Innenspannung





	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	58 - 98	211	SZI 20-10	0123164	17	35	50	20	M6	22	M12	Stahl	1.6
	82 - 127	211	SZI 20-11	0123165	17	40	50	20	M6	22	M12	Stahl	2
	113 - 158	211	SZI 20-12	0123166	17	40	50	20	M6	22	M12	Stahl	1.7

Krallenbacken für Stangenspannung



	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	12 - 46	208	SZA-ST 20-1	0175101	17	35	45	35	22	M12	Stahl	1.5

SCHUNK Spannbacken für KFV 200



QUENTES Kunststoffbacken

	Spannbereich ØD	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Max. Anzugsmo- ment [Nm]	Schrauben	m/Satz [kg]
	20 - 65	TRQ 200-1	0150001	17	40	55	70	19		M12	0.66
	85 - 169	TRQ 200-2	0150002	17	40	64	79	19		M12	0.93
		QUENTES 10-3	0150100						8		
		QUENTES 20-3	0150200						8		

Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWB-SM 200	0169101	17	140	64	200	60	50	69.5	35	22	M12	Stahl	8.6
	SWB-SM 201	0169106	17	140	64	200	75	65	69.5	35	22	M12	Stahl	10.8
	SWB-SA 200	0170101	17	140	50	200	58	48	72.5	35	22	M12	Aluminium	3.4
	SWB-SA 201	0170106	17	140	50	200	75	65	72.5	35	22	M12	Aluminium	4.2

Verzahnte Stangen



	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	SBM-ST 170	0112170	17	40	60	420	Stahl	7.6
	SBM-ST 171	0112171	17	40	80	420	Stahl	10.2
	SBM-ST 172	0112172	17	40	100	420	Stahl	12.8
	SBM-STA 170	0112173	17	40	60	420	Aluminium	2.8




Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für KfV 200

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWBL 200	0120153	17	35	40	98	4	15	22	M12	Stahl	2.6
	CWB 200	0100006	17	40	40	90		25	22	M12	Stahl	2.7
	SWB 200	0120104	17	40	60	90		25	22	M12	Stahl	4.1
	SWB-AL 200	0168101	17	40	60	90		25	22	M12	Aluminium	1.5

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmoment [Nm]
	NS 120	0140101	17	23	9		M12	M12 x 30	70
	NK 121	0145100	17	23	9	22	M12	M12 x 30	70



Technische Beratung und Verkauf: Tel. +49-7133-103-2750