




# SCHUNK chuck jaws for KFH-NC 160


## Full Grip Jaws

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | B1<br>[mm] | Ø D<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-------------|-----------|------------|-----------|-----------|-----------|--------|----------|---------------|
|  | SWB-SM 160  | 0169100 | 17        | 120       | 40         | 160         | 60        | 50         | 59.5      | 25        | 22        | M12    | Steel    | 5.7           |
|  | SWB-SA 160  | 0170100 | 17        | 120       | 40         | 165         | 58        | 48         | 59.5      | 22        | 22        | M12    | Aluminum | 2.2           |

## Hard Stepped Top Jaws

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|--------|----------|---------------|
|  | SHB 175     | 0121103 | 17        | 35        | 44        | 64.7      | 10        | 28        | 19        |           | M12    | Steel    | 1.2           |
|                                                                                   | SHB 200     | 0121104 | 17        | 40        | 49        | 72.5      | 12        | 18        | 19        | 19        | M12    | Steel    | 1.6           |

## Jaw blanks



|                                                                                     | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Min. distance<br>a (jaw tip up<br>to first hole)<br>[mm] | Min. distance<br>b (first up to<br>second hole)<br>[mm] | Screws | Material | m/piece<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|----------------------------------------------------------|---------------------------------------------------------|--------|----------|-----------------|
|  | SBM 31      | 0112100 | 17        | 40        | 40        | 70        | 12                                                       | 22                                                      | M12    | Steel    | 0.9             |
|                                                                                     | SBM 32      | 0112101 | 17        | 40        | 40        | 90        | 12                                                       | 22                                                      | M12    | Steel    | 1.1             |
|                                                                                     | SBM 33      | 0112102 | 17        | 40        | 40        | 105       | 12                                                       | 22                                                      | M12    | Steel    | 1.2             |
|                                                                                     | SBM 34      | 0112103 | 17        | 40        | 60        | 70        | 12                                                       | 22                                                      | M12    | Steel    | 1.3             |
|                                                                                     | SBM 35      | 0112104 | 17        | 40        | 60        | 90        | 12                                                       | 22                                                      | M12    | Steel    | 1.7             |
|                                                                                     | SBM 36      | 0112105 | 17        | 40        | 60        | 105       | 12                                                       | 22                                                      | M12    | Steel    | 2               |
|                                                                                     | SBM 361     | 0112136 | 17        | 40        | 60        | 120       | 12                                                       | 22                                                      | M12    | Steel    | 2.2             |
|                                                                                     | SBM 3610    | 0112107 | 17        | 40        | 100       | 90        | 12                                                       | 22                                                      | M12    | Steel    | 2.7             |
|                                                                                     | SBM 3612    | 0112108 | 17        | 40        | 120       | 90        | 12                                                       | 22                                                      | M12    | Steel    | 3.4             |
|                                                                                     | SBM 3615    | 0112139 | 17        | 50        | 80        | 90        | 12                                                       | 22                                                      | M12    | Steel    | 2.7             |
|                                                                                     | SBM 368     | 0112106 | 17        | 40        | 80        | 90        | 12                                                       | 22                                                      | M12    | Steel    | 2.3             |
|                                                                                     | SBM 37      | 0112109 | 17        | 60        | 60        | 70        | 12                                                       | 22                                                      | M12    | Steel    | 1.9             |
|                                                                                     | SBM 38      | 0112110 | 17        | 60        | 60        | 90        | 12                                                       | 22                                                      | M12    | Steel    | 2.4             |
|                                                                                     | SBM 40      | 0112111 | 17        | 80        | 60        | 90        | 12                                                       | 22                                                      | M12    | Steel    | 3.3             |




Technical advice and sales: Tel. +49-7133-103-2750

# SCHUNK chuck jaws for KFH-NC 160




## QUENTES fiberglass jaws

|                                                                                   | Clamping range ØD | Description  | ID      | N [mm] | B [mm] | H [mm] | L [mm] | b [mm] | Max. tightening torque [Nm] | Screws | m/set [kg] |
|-----------------------------------------------------------------------------------|-------------------|--------------|---------|--------|--------|--------|--------|--------|-----------------------------|--------|------------|
|  | 60 - 135          | TRQ 200-2    | 0150002 | 17     | 40     | 64     | 79     | 19     |                             | M12    | 0.93       |
|  |                   | QUINTES 20-3 | 0150200 |        |        |        |        |        | 8                           |        |            |

## Serrated bars

|                                                                                    | Description | ID      | N [mm] | B [mm] | H [mm] | L [mm] | Material | m/piece [kg] |
|------------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|--------|----------|--------------|
|   | SBM-ST 170  | 0112170 | 17     | 40     | 60     | 420    | Steel    | 7.6          |
|                                                                                    | SBM-ST 171  | 0112171 | 17     | 40     | 80     | 420    | Steel    | 10.2         |
|                                                                                    | SBM-ST 172  | 0112172 | 17     | 40     | 100    | 420    | Steel    | 12.8         |
|  | SBM-STA 170 | 0112173 | 17     | 40     | 60     | 420    | Aluminum | 2.8          |

## Soft Top Jaws

|                                                                                     | Description | ID      | N [mm] | B [mm] | H [mm] | L [mm] | a1 [mm] | a [mm] | b [mm] | Screws | Material | m/set [kg] |
|-------------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|--------|---------|--------|--------|--------|----------|------------|
|  | SWBL 160    | 0120151 | 17     | 35     | 40     | 78     | 4       | 15     | 22     | M12    | Steel    | 1.9        |
|  | CWB 160     | 0100005 | 17     | 35     | 40     | 70     |         | 15     | 22     | M12    | Steel    | 1.7        |
|                                                                                     | SWB 160     | 0120102 | 17     | 40     | 60     | 70     |         | 15     | 22     | M12    | Steel    | 3.1        |
|  | SWB-AL 160  | 0168100 | 17     | 40     | 60     | 70     |         | 15     | 22     | M12    | Aluminum | 1.2        |



Technical advice and sales: Tel. +49-7133-103-2750

# SCHUNK chuck jaws for KFH-NC 160

## T-nut

|                                                                                   | Description | ID      | S<br>[mm] | H<br>[mm] | H1<br>[mm] | G   | Cyl.-screw | Max. adm.<br>tightening torque<br>[Nm] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-----|------------|----------------------------------------|
|  | NS 124      | 0142101 | 17        | 22        | 9          | M12 | M12 x 25   | 70                                     |



Technical advice and sales: Tel. +49-7133-103-2750