



SCHUNK chuck jaws for KZF-ES 315


Jaw blanks

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/piece [kg]
	SBM 50	0112126	25.5	60	60	140	20	35	M20	Steel	4
	SBM 51	0112127	25.5	60	80	140	20	35	M20	Steel	5
	SBM 52	0112128	25.5	60	100	140	20	35	M20	Steel	6.5
	SBM 53	0112129	25.5	60	100	155	20	35	M20	Steel	7.2
	SBM 531	0112138	25.5	60	100	195	20	35	M20	Steel	9.1
	SBM 5312	0112130	25.5	60	120	155	20	35	M20	Steel	8.7
	SBM 5315	0112131	25.5	58	160	155	20	35	M20	Steel	11.5
	SBM 5320	0112132	25.5	58	200	155	20	35	M20	Steel	14.2
	SBM 57	0112134	25.5	80	80	155	20	35	M20	Steel	7.2
	SBM 58	0112135	25.5	100	100	155	20	35	M20	Steel	11.6

Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 250	0112190	25.5	60	100	420	Steel	19.2
	SBM-ST 251	0112191	25.5	58	160	420	Steel	30.9
	SBM-STA 250	0112187	25.5	60	100	420	Aluminum	7

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	2 SWK 250	0126103	25.5	80	80	110	20	35	M20	Steel	9

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NS 200	0140103	25.5	29	11	M20	M20 x 40	220



Technical advice and sales: Tel. +49-7133-103-2750