



Hand in hand for tomorrow



Product data sheet

Manual change system CMS 063

Flexible. Compact. Intuitive.

Manual change system CMS

User-friendly manual change system with extensive complementary portfolio

Field of application

Ideally suited for use in the flexible production and assembly of products with a comprehensive range of variants in which reliable manual changes are required. The system is suitable for use on robots as well as for stationary applications.

Advantages – Your benefits

Series with six unit sizes for optimal size selection and a broad application range

ISO mounting pattern for easy assembly to most types of robots without needing additional adapter plates

Wide range of signal, pneumatic, fluid and communication modules can be screwed on directly for universal energy transmission options

Optional locking and presence monitoring integrated in the housing for all sizes

Integrated air feed-throughs for a reliable power supply of the handling modules and tools with pneumatic and vacuum, can be used radially and axially

Basic version without integrated air feed-through and sensor option available for simple and cost-sensitive applications



Sizes
Quantity: 6



Handling weight
9 .. 58 kg



Moment load Mx
22.5 .. 478 Nm




Moment load Mz
15 .. 465 Nm

Functional description

The manual change system (CMS) consists of a change head (CMS-K) and a change adapter (CMS-A). Closing the hand lever provides a form-fit lock that is free from play between the change head and the change adapter using a pin and without the need for any additional tools. Opening the hand lever unlocks the system, allowing the change adapter to be removed. End effectors can be

supplied with compressed air or vacuum via integrated pneumatic feed-throughs. In addition, there is an identically constructed variant without pneumatic feed-throughs and without a monitoring option (CMS-B). In both product variants, the tool can be supplied with other media such as electrical signals or fluids through optional modules.



- ① **Locking lever**
Proven technology for manual actuation without additional tools
- ② **Locking pin**
made of corrosion-free steel for easy and secure locking
- ③ **ISO mounting pattern**
Master and adapter side, for easy assembly to most types of robots without needing additional adapter plates
- ④ **Integrated locking and tool presence monitoring**
optional, for process-reliable monitoring of the locking condition and tool presence
- ⑤ **Integrated air feed-through**
all can be used radially and axially for pneumatics and vacuum.
- ⑥ **Standardized screw-on surface for direct attachment of electrical, pneumatic and fluid modules**
Enables versatile energy transmission for controlling a wide range of tools

General notes about the series

Actuation: Manual via locking lever


Operating principle: The head and adapter are locked and unlocked with a pin by operating the manual lever.

Housing: The housing consists of high-strength, hard-coated aluminum alloy. The functional components are made of hardened steel.

Warranty: 24 months

Harsh environmental conditions: Please note that use under harsh environmental conditions (e.g. in the coolant area, cast and grinding dust) can considerably reduce the service life of the units, and we will not take over any warranty. However, in many cases we can find a solution. Please contact us for assistance.

Handling weight: is the weight of the total load attached to the flange. When designing, the permissible forces and moments have to be paid attention to. Please note that exceeding the recommended handling weight will shorten the lifespan.



Application example

Tool for handling and assembling small to medium-sized workpieces, consisting of manual change system and gripper.

- ① Manual change system CMS
- ② 2-finger parallel gripper PGN-plus-P with customized gripper fingers
- ③ 2-finger parallel gripper MPG-plus with customized gripper fingers

SCHUNK offers more ...

The following components make the product even more productive – the suitable addition for the highest functionality, flexibility, reliability, and controlled production.



Rotary feed-through



Compensation unit



Anti-collision and overload protection sensor



Universal gripper



Inductive proximity switch



Optional modules COS

① For more information on these products can be found on the following product pages or at [schunk.com](https://www.schunk.com).

Options and special information


Basic version: simplified version without integrated air ducts and without monitoring options for maximum economy.

SHA version (-N): with the same tool-sided screw connection diagram as the predecessor product SHA. Allows simple replacement of existing SHS systems with the CMS without changing the customer-specific tools. The SHA version differs from the basic design only on the adapter side (CMS-A).

Food-grade lubrication: The product contains food-compliant lubricants as standard. The requirements of EN 1672-2:2020 are not fully met. The relevant NSF certificates are available at <https://info.nsf.org/USDA/Listings.asp> using the lubricant information in the operating manual.




Load diagram



Maximum handling weight as a function of acceleration and lever arm (by M_x/M_y). The diagram does not replace the technical design.

Dimensions and maximum loads



① This is the sum of all static loads that are permitted to act on the change system to ensure error-free functioning.

Technical data


Description		CMS 063-K	CMS 063-A
		Manual change head	Manual change adapter
ID		1545316	1545318
Recommended handling weight	[kg]	18	18
Lock sensing		optional	
Tool presence monitoring		optional	
Repeat accuracy	[mm]	0.02	0.02
Weight	[kg]	0.49	0.27
Number of pneumatic feed-throughs		6	6
Feed-throughs for radial use		6	6
Air connection thread pneumatic feed-through (radial)		G1/8"	G1/8"
Robot-side coupling flange		ISO 9409-1-63-4-M6	
Coupling flange, tool side			ISO 9409-1-63-4-M6
Dimensions X x Y x Z*	[mm]	80/101/28.5	80/88/18
Min./max. ambient temperature	[°C]	5/60	5/60
Dimensions Ø D x Z*	[mm]		- x 18
Screw connection diagram		K	K
max. static tensile force F_z	[N]	1000	1000
Max. dynamic moment M_x/M_y	[Nm]	75	75
Max. dynamic moment M_z	[Nm]	48	48
Options and their characteristics			
Basic version		CMS 063-K-B	CMS 063-A-B
ID		1545321	1545322
Lock sensing		not possible	
Weight	[kg]	0.5	0.3
SHA version (-N)			CMS 063-A-N
ID			1545319
Weight	[kg]		0.27
Tool-side connection			Ø63, 4xM8

* Please note that the heights of the change master (ZK) and change adapter (ZA) differ. The sum represents the total height of a coupled change system.

[illegible]


① Robot-side connection	③③ DIN ISO-9409 bolt circle
② Tool-side connection	⑦③ Fit for centering pins
①⑨ Mounting surface for options	⑦⑧ Fit for centering
②⑤ Pneumatic feed-throughs	

SHA version (-N)



The SHA version has the same screw-on pattern on the tool side as the predecessor product SHS. Thus, existing SHS systems can be replaced by the CMS without changing the tools.


Pneumatic feed-through



- 90 Feed-through axial
- 91 Feed-through radial


The change system features feed-throughs for pneumatics or vacuum integrated in the housing. They can be used hose-free via an adapter plate (axial) or with a hose (radial).

Electric feed-through module



① For detailed information, see the "COS" chapter in the catalog, or visit schunk.com.

Centering collar on CMS-K




- 1 Robot-side connection
- 78 Fit for centering
- 90 Centring disc

Description	ID
Centering disc	
ZB-CMS-063-K CENTERING COLLAR	1574473

① Serves as a fitting collar for centering on mechanical interfaces, e. g. on the robot.

Cable plug/cable extension




- 90 Plug/socket straight
 91 Connector/angled socket
 92 Connector/straight socket with extension cable
 93 Connector/angled socket with extension cable

Other cable lengths on request.

Description	ID	Length [m]
Angled cable connector, robot-side		
KAS-19B-K-90-C	0301294	
Angled cable connector, tool-side		
KAS-19B-A-90-C	0301295	
Angled cable connector with cable, robot-side		
KA BW19B-L 19P-0300	0302179	3
KA BW19B-L 19P-0500	0302190	5
KA BW19F-L 19P-0500	0302172	5
KA BW19F-L 19P-1000	0302173	10
KA BW26B-L 26P-0300	0302185	3
KA BW26B-L 26P-0500	0302186	5
Angled cable connector with cable, tool-side		
KA SW19B-L 19P-0300	0302191	3
KA SW19F-L 19P-0300	0302175	3
KA SW26B-L 26P-0300	0302187	3
Straight cable connector, robot-side		
KAS-19B-K-0-C	0301283	
Straight cable connector, tool-side		
KAS-19B-A-0-C	0301284	
Straight cable connector with cable, robot-side		
KA BG19B-L 19P-0300	0302176	3
KA BG19B-L 19P-0500	0302177	5
KA BG19F-L 19P-0500	0302170	5
KA BG19F-L 19P-1000	0302171	10
KA BG26B-L 26P-0300	0302192	3
KA BG26B-L 26P-0500	0302193	5
Straight cable connector with cable, tool-side		
KA SG19B-L 19P-0300	0302178	3
KA SG19F-L 19P-0300	0302174	3
KA SG26B-L 26P-0300	0302184	3
Cable extension		
KA BG08-L 8AP-0500	0302180	
KA BW08-L 8AP-0500	0302182	
KA SG08-L 8AP-0200	0302181	
KA SW08-L 8AP-0200	0302183	

① Detailed information and further cable connectors can be found at schunk.com

Monitoring via inductive proximity switches



The CMS-K is prepared for locking monitoring as well as tool presence. One attachment kit each is required for this. Each attachment kit includes one sensor and one bracket incl. a screw.

Description	ID	
Robot side		
AS-CMS-K-IN30K	1548743	

① This attachment kit is optional and must be ordered separately as an accessory.



SCHUNK SE & Co. KG

Spanntechnik

Greiftechnik

Automatisierungstechnik

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

info@de.schunk.com

schunk.com

Folgen Sie uns | *Follow us*

