



SCHUNK chuck jaws for LVE 630



Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB 400	0121107	25.5	60	75	140	18	53	31	31	M20	Steel	8

Jaw blanks

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Min. distance a (jaw tip up to first hole) [mm]	Min. distance b (first up to second hole) [mm]	Screws	Material	m/piece [kg]
	SBM 50	0112126	25.5	60	60	140	20	35	M20	Steel	4
	SBM 51	0112127	25.5	60	80	140	20	35	M20	Steel	5
	SBM 52	0112128	25.5	60	100	140	20	35	M20	Steel	6.5
	SBM 53	0112129	25.5	60	100	155	20	35	M20	Steel	7.2
	SBM 531	0112138	25.5	60	100	195	20	35	M20	Steel	9.1
	SBM 5312	0112130	25.5	60	120	155	20	35	M20	Steel	8.7
	SBM 5315	0112131	25.5	58	160	155	20	35	M20	Steel	11.5
	SBM 5320	0112132	25.5	58	200	155	20	35	M20	Steel	14.2
	SBM 57	0112134	25.5	80	80	155	20	35	M20	Steel	7.2
	SBM 58	0112135	25.5	100	100	155	20	35	M20	Steel	11.6

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	CWB 400	0100008	25.5	60	80	140	30	35	M20	Steel	12.6
	SWB 400	0120107	25.5	60	90	155	30	35	M20	Steel	16
	SWB-AL 400	0168103	25.5	60	100	155	30	35	M20	Aluminum	6.4

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NS 201	0142103	25.5	33.7	15.5	M20	M20 x 45	300



Technical advice and sales: Tel. +49-7133-103-2750