




OPUS-H3

**Hydraulically actuated open-
center cylinder**

Open-center cylinders for hydraulically operated power lathe chucks with large through-hole, wide adjustment range and shortest switching times.

The clamping cylinder OPUS-H3 is the ideal standard cylinder with a large through-hole for all conventional power lathe chucks. The clamping cylinder is designed for high rotational speeds and can be operated at a hydraulic pressure of up to 45 bar. Two proximity switches allow easy adjustment and monitoring of the clamping stroke via an integrated control cam.



Advantages – Your benefits

- + Integrated check valve**
Temporarily maintains the pressure in the hydraulic cylinder in case of pipe failure
- + Compact design**
Easy integration in existing lathes
- + Large through-hole**
Ideal for machining of rods and feeding material from the back
- + Long actuating stroke**
Suitable for actuation of all standard power chucks
- + Integrated control cam for stroke monitoring**
Two proximity switches allow easy adjustment and monitoring of the clamping stroke

Technical data

Description	Max. rotational speed [min ⁻¹]	Piston stroke [mm]	Through-hole [mm]	Max. pressure [bar]	Pull force at 45 bar [kN]
OPUS-H3 70-37	8000	26	37.5	45	31
OPUS-H3 102-46	7000	25	46.5	45	46
OPUS-H3 130-52	6300	25	52.5	45	58
OPUS-H3 150-67	5500	29	67.5	45	68
OPUS-H3 170-77	5000	29	77	45	76
OPUS-H3 200-86	4500	34	86	45	88
OPUS-H3 225-95	4000	34	95	45	100
OPUS-H3 250-110	3600	35	110.5	45	110
OPUS-H3 320-127	3200	40	127.5	45	144


Open-center cylinder

Scope of delivery

Open-center cylinder, coolant collector, stroke control, bracket for sensors and operating manual; without sensors, without mounting screws

Technical data

ID	Max. rotational speed [min ⁻¹]	Piston surface [cm ²]	Piston stroke [mm]	Through-hole [mm]	Max. pressure [bar]	Pull force at 45 bar [kN]	Oil leakage rate [l/min]	Moment of inertia [kgm ²]	Power consumption [kW]	Weight [kg]
1360385	6300	131	25	52.5	45	58	3.5	0.04	1.2	15





**H.-D. SCHUNK GmbH & Co.
Spanntechnik KG**

Lothringer Str. 23
D-88512 Mengen
Tel. +49-7572-7614-1300
Fax +49-7572-7614-1039
CMM@de.schunk.com
schunk.com