




GZB-S KD

GZB-S Ø 12 KD
Intermediate sleeves




- ① O-ring seal
- ② Adjustable stop/length adjustment



Technical data

ID	D1 [mm/Inch]	D2 [mm]	D3 [mm]	L1 [mm]	L10 [mm]	Weight [kg]
0207910	3 mm	12 mm	16.5	45	2	0.1
0207911	4 mm	12 mm	16.5	45	2	0.1
0207912	5 mm	12 mm	16.5	45	2	0.1
0207913	6 mm	12 mm	16.5	45	2	0.1
20024051	7 mm	12 mm	16.5	45	2	0.1
0207915	8 mm	12 mm	16.5	45	2	0.1
20019450	9 mm	12 mm	16.5	45	2	0.1
0207917	10 mm	12 mm	16.5	45	2	0.1
0224429	1/8"	12 mm	16.5	45	2	0.1
0224430	3/16"	12 mm	16.5	45	2	0.1
0224431	1/4"	12 mm	16.5	45	2	0.1
0224432	5/16"	12 mm	16.5	45	2	0.1
0224433	3/8"	12 mm	16.5	45	2	0.1

Additional sizes and customized designs are available upon request
Version coolant-proof up to max. 80 bar – for internal coolant supply
Run-out accuracy: ≤ 0.003 mm



- ① O-ring seal
- ② Adjustable stop/length adjustment




Technical data

ID	D1 [mm]	D2 [mm]	D3 [mm]	L1 [mm]	L10 [mm]	Weight [kg]
0207920	3 mm	20 mm	24	50.5	2	0.1
0207921	4 mm	20 mm	24	50.5	2	0.1
0207922	5 mm	20 mm	24	50.5	2	0.1
0207923	6 mm	20 mm	24	50.5	2	0.1
0207924	7 mm	20 mm	24	50.5	2	0.1
0207925	8 mm	20 mm	24	50.5	2	0.1
0207926	9 mm	20 mm	24	50.5	2	0.1
0207927	10 mm	20 mm	24	50.5	2	0.1
0207928	11 mm	20 mm	24	50.5	2	0.1
0207929	12 mm	20 mm	24	50.5	2	0.1
0207930	13 mm	20 mm	24	50.5	2	0.1
0207931	14 mm	20 mm	24	50.5	2	0.1
0207932	15 mm	20 mm	24	50.5	2	0.1
0207933	16 mm	20 mm	24	50.5	2	0.1
20051938	17 mm	20 mm	24	50.5	2	0.1
20034637	18 mm	20 mm	24	50.5	2	0.1

Additional sizes and customized designs are available upon request
Version coolant-proof up to max. 80 bar – for internal coolant supply
Run-out accuracy: ≤ 0.003 mm

GZB-S Ø 20 KD
Intermediate sleeves




- ① O-ring seal
- ② Adjustable stop/length adjustment



Technical data

ID	D1 [Inch]	D2 [mm]	D3 [mm]	L1 [mm]	L10 [mm]	Weight [kg]
0224434	1/8"	20 mm	24	50.5	2	0.1
0224435	3/16"	20 mm	24	50.5	2	0.1
0224436	1/4"	20 mm	24	50.5	2	0.1
0224437	5/16"	20 mm	24	50.5	2	0.1
0224438	3/8"	20 mm	24	50.5	2	0.1
0224439	7/16"	20 mm	24	50.5	2	0.1
0224440	1/2"	20 mm	24	50.5	2	0.1
0224441	9/16"	20 mm	24	50.5	2	0.1
0224442	5/8"	20 mm	24	50.5	2	0.1

Additional sizes and customized designs are available upon request
Version coolant-proof up to max. 80 bar – for internal coolant supply
Run-out accuracy: ≤ 0.003 mm




Technical data

ID	D1 [mm]	D2 [mm]	D3 [mm]	L1 [mm]	L10 [mm]	Weight [kg]
0207892	6 mm	22 mm	25	50.5	2	0.2
0207893	8 mm	22 mm	25	50.5	2	0.2
0207894	10 mm	22 mm	25	50.5	2	0.2
0207895	12 mm	22 mm	25	50.5	2	0.2
0207896	14 mm	22 mm	25	50.5	2	0.2
0207897	16 mm	22 mm	25	50.5	2	0.2

Additional sizes and customized designs are available upon request
Version coolant-proof up to max. 80 bar – for internal coolant supply
Run-out accuracy: ≤ 0.003 mm


GZB-S Ø 25 KD
Intermediate sleeves



Technical data

ID	D1 [mm]	D2 [mm]	D3 [mm]	L1 [mm]	L10 [mm]	Weight [kg]
0207865	6 mm	25 mm	29	54.5	2	0.1
0207866	8 mm	25 mm	29	54.5	2	0.1
0207867	10 mm	25 mm	29	54.5	2	0.1
0207868	12 mm	25 mm	29	54.5	2	0.1
0207869	14 mm	25 mm	29	54.5	2	0.1
0207870	16 mm	25 mm	29	54.5	2	0.1
0207871	18 mm	25 mm	29	54.5	2	0.1
0207872	20 mm	25 mm	29	54.5	2	0.1

Additional sizes and customized designs are available upon request
Version coolant-proof up to max. 80 bar – for internal coolant supply
Run-out accuracy: ≤ 0.003 mm



- ① O-ring seal
- ② Adjustable stop/length adjustment




Technical data

ID	D1 [mm]	D2 [mm]	D3 [mm]	L1 [mm]	L10 [mm]	Weight [kg]
20038806	3 mm	32 mm	35.5	60.5	2	0.3
20027707	4 mm	32 mm	35.5	60.5	2	0.3
20027602	5 mm	32 mm	35.5	60.5	2	0.3
0207940	6 mm	32 mm	35.5	60.5	2	0.3
20027601	7 mm	32 mm	35.5	60.5	2	0.3
0207941	8 mm	32 mm	35.5	60.5	2	0.3
20019807	9 mm	32 mm	35.5	60.5	2	0.3
0207942	10 mm	32 mm	35.5	60.5	2	0.3
20019481	11 mm	32 mm	35.5	60.5	2	0.3
0207943	12 mm	32 mm	35.5	60.5	2	0.3
20027597	13 mm	32 mm	35.5	60.5	2	0.3
0207944	14 mm	32 mm	35.5	60.5	2	0.3
20030304	15 mm	32 mm	35.5	60.5	2	0.3
0207945	16 mm	32 mm	35.5	60.5	2	0.3
20027594	17 mm	32 mm	35.5	60.5	2	0.3
0207946	18 mm	32 mm	35.5	60.5	2	0.3
20012603	19 mm	32 mm	35.5	60.5	2	0.3
0207947	20 mm	32 mm	35.5	60.5	2	0.3
20012604	21 mm	32 mm	35.5	60.5	2	0.3
20011792	22 mm	32 mm	35.5	60.5	2	0.3
20011793	23 mm	32 mm	35.5	60.5	2	0.3
20012646	24 mm	32 mm	35.5	60.5	2	0.3
0207948	25 mm	32 mm	35.5	60.5	2	0.3
20020442	26 mm	32 mm	35.5	60.5	2	0.3
20021164	28 mm	32 mm	35.5	60.5	2	0.3
20031546	30 mm	32 mm	35.5	60.5	2	0.3

Additional sizes and customized designs are available upon request
Version coolant-proof up to max. 80 bar – for internal coolant supply
Run-out accuracy: ≤ 0.003 mm

GZB-S Ø 32 KD
Intermediate sleeves




- ① O-ring seal
- ② Adjustable stop/length adjustment



Technical data

ID	D1 [Inch]	D2 [mm]	D3 [mm]	L1 [mm]	L10 [mm]	Weight [kg]
0224450	9/16"	32 mm	35.5	60.5	2	0.3
0224451	5/8"	32 mm	35.5	60.5	2	0.3
0224452	11/16"	32 mm	35.5	60.5	2	0.3
0224453	3/4"	32 mm	35.5	60.5	2	0.3
0224454	13/16"	32 mm	35.5	60.5	2	0.3
0224455	7/8"	32 mm	35.5	60.5	2	0.3
0224456	15/16"	32 mm	35.5	60.5	2	0.3
0224457	1"	32 mm	35.5	60.5	2	0.3

Additional sizes and customized designs are available upon request
Version coolant-proof up to max. 80 bar – for internal coolant supply
Run-out accuracy: ≤ 0.003 mm



- ① O-ring seal
- ② Adjustable stop/length adjustment




Technical data

ID	D1 [mm/Inch]	D2 [Inch]	D3 [mm]	L1 [mm]	L10 [mm]	Weight [kg]
0224381	3 mm	1/2"	16.5	45	2	0.1
0224382	4 mm	1/2"	16.5	45	2	0.1
0224383	5 mm	1/2"	16.5	45	2	0.1
0224384	6 mm	1/2"	16.5	45	2	0.1
0224385	8 mm	1/2"	16.5	45	2	0.1
0224376	1/8"	1/2"	16.5	45	2	0.1
0224377	3/16"	1/2"	16.5	45	2	0.1
0224378	1/4"	1/2"	16.5	45	2	0.1
0224379	5/16"	1/2"	16.5	45	2	0.1
0224380	3/8"	1/2"	16.5	45	2	0.1

Additional sizes and customized designs are available upon request
Version coolant-proof up to max. 80 bar – for internal coolant supply
Run-out accuracy: ≤ 0.003 mm

GZB-S Ø 3/4" KD

Intermediate sleeves




- ① O-ring seal
- ② Adjustable stop/length adjustment



Technical data

ID	D1 [mm/Inch]	D2 [Inch]	D3 [mm]	L1 [mm]	L10 [mm]	Weight [kg]
0224395	3 mm	3/4"	24	50.5	2	0.1
0224396	4 mm	3/4"	24	50.5	2	0.1
0224397	5 mm	3/4"	24	50.5	2	0.1
0224398	6 mm	3/4"	24	50.5	2	0.1
0224399	8 mm	3/4"	24	50.5	2	0.1
0224400	10 mm	3/4"	24	50.5	2	0.1
0224401	12 mm	3/4"	24	50.5	2	0.1
0224402	14 mm	3/4"	24	50.5	2	0.1
20023434	16 mm	3/4"	24	50.5	2	0.1
0224386	1/8"	3/4"	24	50.5	2	0.1
0224387	3/16"	3/4"	24	50.5	2	0.1
0224388	1/4"	3/4"	24	50.5	2	0.1
0224389	5/16"	3/4"	24	50.5	2	0.1
0224390	3/8"	3/4"	24	50.5	2	0.1
0224391	7/16"	3/4"	24	50.5	2	0.1
0224392	1/2"	3/4"	24	50.5	2	0.1
0224393	9/16"	3/4"	24	50.5	2	0.1
0224394	5/8"	3/4"	24	50.5	2	0.1

Additional sizes and customized designs are available upon request
 Version coolant-proof up to max. 80 bar – for internal coolant supply
 Run-out accuracy: ≤ 0.003 mm



- ① O-ring seal
- ② Adjustable stop/length adjustment




Technical data

ID	D1 [mm]	D2 [inch]	D3 [mm]	L1 [mm]	L10 [mm]	Weight [kg]
0224421	8 mm	1 1/4"	35.5	60.5	2	0.3
0224422	10 mm	1 1/4"	35.5	60.5	2	0.3
0224423	12 mm	1 1/4"	35.5	60.5	2	0.3
0224424	14 mm	1 1/4"	35.5	60.5	2	0.3
0224425	16 mm	1 1/4"	35.5	60.5	2	0.3
0224426	18 mm	1 1/4"	35.5	60.5	2	0.3
0224427	20 mm	1 1/4"	35.5	60.5	2	0.3
0224428	25 mm	1 1/4"	35.5	60.5	2	0.3

Additional sizes and customized designs are available upon request
Version coolant-proof up to max. 80 bar – for internal coolant supply
Run-out accuracy: ≤ 0.003 mm

GZB-S Ø 1 1/4" KD
Intermediate sleeves



- ① O-ring seal
- ② Adjustable stop/length adjustment



Technical data

ID	D1 [Inch]	D2 [Inch]	D3 [mm]	L1 [mm]	L10 [mm]	Weight [kg]
0224404	1/4"	1 1/4"	35.5	60.5	2	0.3
0224405	5/16"	1 1/4"	35.5	60.5	2	0.3
0224406	3/8"	1 1/4"	35.5	60.5	2	0.3
0224407	7/16"	1 1/4"	35.5	60.5	2	0.3
0224408	1/2"	1 1/4"	35.5	60.5	2	0.3
0224409	9/16"	1 1/4"	35.5	60.5	2	0.3
0224410	5/8"	1 1/4"	35.5	60.5	2	0.3
0224411	11/16"	1 1/4"	35.5	60.5	2	0.3
0224412	3/4"	1 1/4"	35.5	60.5	2	0.3
0224413	13/16"	1 1/4"	35.5	60.5	2	0.3
0224414	7/8"	1 1/4"	35.5	60.5	2	0.3
0224415	15/16"	1 1/4"	35.5	60.5	2	0.3
0224416	1"	1 1/4"	35.5	60.5	2	0.3

Additional sizes and customized designs are available upon request
Version coolant-proof up to max. 80 bar – for internal coolant supply
Run-out accuracy: ≤ 0.003 mm



SCHUNK SE & Co. KG

Spanntechnik

Greiftechnik

Automatisierungstechnik

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

CMS@de.schunk.com

schunk.com