




OPUS-H3

**Przelotowy siłownik
uruchamiany hydraulicznie**

Przelotowe siłowniki do uruchamianych hydraulicznie uchwytów tokarskich z dużym otworem przelotowym, o szerokim zakresie regulacji i najkrótszych czasach przełączania.

Siłownik zaciskowy OPUS-H3 to standardowy siłownik z dużym otworem przelotowym idealny do wszystkich konwencjonalnych zasilanych uchwytów tokarskich. Siłownik zaciskowy jest zaprojektowany do pracy przy wysokich prędkościach obrotowych i może działać przy ciśnieniu hydraulicznym do 45 barów. Dwa czujniki zbliżeniowe umożliwiają łatwą regulację i monitorowanie skoku mocowania poprzez wbudowaną krzywkę sterującą.



Zalety – Korzyści dla użytkownika

- + Wbudowany zawór zwrotny**
W razie awarii przewodu hydraulicznego tymczasowo utrzymuje ciśnienie w cylindrze hydraulicznym
- + Kompaktowa konstrukcja**
łatwe dopasowanie do tokarek
- + Duży otwór przelotowy**
Idealny do obróbki prętów i podawania materiału od tyłu
- + Długi skok aktywujący**
Nadaje się do uruchamiania wszystkich standardowych zasilanych uchwytów tokarskich
- + Wbudowana krzywka do monitorowania skoku**
Dwa czujniki zbliżeniowe umożliwiają łatwą regulację i monitorowanie skoku mocowania

Dane techniczne

Opis	Maks. prędkość obrotowa [min ⁻¹]	Skok tłoka [mm]	Otwór przelotowy [mm]	Maks. ciśnienie [bar]	Siła ciągnąca przy ciśnieniu 45 barów [kN]
OPUS-H3 70-37	8000	26	37.5	45	31
OPUS-H3 102-46	7000	25	46.5	45	46
OPUS-H3 130-52	6300	25	52.5	45	58
OPUS-H3 150-67	5500	29	67.5	45	68
OPUS-H3 170-77	5000	29	77	45	76
OPUS-H3 200-86	4500	34	86	45	88
OPUS-H3 225-95	4000	34	95	45	100
OPUS-H3 250-110	3600	35	110.5	45	110
OPUS-H3 320-127	3200	40	127.5	45	144

Zakres dostawy

Dane techniczne

Technical drawing of a 100 bar pressure washer, showing front, side, and detail views with dimensions in mm and inches.

Front View Dimensions:

- Overall width: 104 mm
- Overall height: 153 mm
- Mounting bracket width: 104 mm
- Mounting bracket height: 36 mm
- Mounting bracket thread: G3/8"

Side View Dimensions:

- Overall length: 203 mm
- Overall height: 127 mm
- Motor housing diameter: Ø190 mm
- Motor housing length: 95 mm
- Motor housing mounting bracket width: 34 mm
- Motor housing mounting bracket height: 11 mm
- Motor housing mounting bracket thread: Ø11
- Motor housing mounting bracket length: -3 ... 31 mm
- Motor housing mounting bracket diameter: Ø105 mm
- Motor housing mounting bracket length: Ø180 h6
- Motor housing mounting bracket length: Ø210
- Motor housing mounting bracket length: Ø234
- Motor housing mounting bracket length: 8 mm
- Motor housing mounting bracket length: 107 mm
- Motor housing mounting bracket length: 146 mm
- Motor housing mounting bracket length: 203 mm
- Motor housing mounting bracket length: 90 mm
- Motor housing mounting bracket length: Ø32
- Motor housing mounting bracket length: Ø32

Detail View Dimensions:

- Detail view Z shows the motor housing mounting bracket with dimensions: 10 mm, 30 mm, 6 mm, 32 mm.
- Detail view Z shows the motor housing mounting bracket with dimensions: Ø86.5, Ø87 H8, M90x2, Ø92 H8, M95x2.



**H.-D. SCHUNK GmbH & Co.
Spanntechnik KG**

Lothringer Str. 23
D-88512 Mengen
Tel. +49-7572-7614-1300
Fax +49-7572-7614-1039
CMM@de.schunk.com
schunk.com