

COS E3A

Customer specific feedthrough module



Hand in hand for tomorrow



COS E3A

Electrical feedthrough module; Signal module

Technical data


- | | |
|---------------------|--------------------------|
| • Ident. -Nr. | 1586991 (M); 1586990 (T) |
| • Mounting pattern | S5 (CPS-005) |
| • Transmission type | Signal |

Signal feedthrough

- | | |
|-----------------------------------|--------------------|
| • Nominal current | Up to 3A |
| • Nominal voltage | Up to 50 V (AC/DC) |
| • Electrical connection | Solder contacts |
| • Electrical connection outlet | Axial |
| • No. of pin contacts | 30 |
| • Weight robot side | 0.022 Kg |
| • Weight tool side | 0.02 Kg |
| • min. / max. ambient temperature | Min 5°C/ max 60°C |


Please contact us with your individual requirement.
You can reach the Select a team at:

Select a hotline
Select an e-mail address



12 Master side

13 Adapter side



12 Master side

90 solder contacts

13 Adapter side

91 solder contacts