



# TENDO WZS GZB-S




Technical data

| ID      | D1<br>[mm] | D2<br>[mm] | D3<br>[mm] | D4<br>[mm] | L1<br>[mm] | L10<br>[mm] | Weight<br>[kg] |
|---------|------------|------------|------------|------------|------------|-------------|----------------|
| 0207655 | 3 mm       | 12         | 17         | 10         | 45         | 8           | 0.1            |
| 0207656 | 4 mm       | 12         | 17         | 10         | 45         | 8           | 0.1            |
| 0207657 | 5 mm       | 12         | 17         | 10         | 45         | 8           | 0.1            |
| 0207658 | 6 mm       | 12         | 17         | 10         | 45         | 8           | 0.1            |
| 0207659 | 7 mm       | 12         | 17         | 10         | 45         | 8           | 0.1            |
| 0207660 | 8 mm       | 12         | 17         | 10         | 45         | 8           | 0.1            |




## Technical data

| ID      | D1<br>[mm] | D2<br>[mm] | D3<br>[mm] | D4<br>[mm] | L1<br>[mm] | L10<br>[mm] | Weight<br>[kg] |
|---------|------------|------------|------------|------------|------------|-------------|----------------|
| 0207685 | 3 mm       | 20         | 25         | 16         | 51         | 10          | 0.1            |
| 0207686 | 4 mm       | 20         | 25         | 16         | 51         | 10          | 0.1            |
| 0207687 | 5 mm       | 20         | 25         | 16         | 51         | 10          | 0.1            |
| 0207688 | 6 mm       | 20         | 25         | 16         | 51         | 10          | 0.1            |
| 0207680 | 7 mm       | 20         | 25         | 16         | 51         | 10          | 0.1            |
| 0207689 | 8 mm       | 20         | 25         | 16         | 51         | 10          | 0.1            |
| 0207681 | 9 mm       | 20         | 25         | 16         | 51         | 10          | 0.1            |
| 0207690 | 10 mm      | 20         | 25         | 16         | 51         | 10          | 0.1            |
| 0207682 | 11 mm      | 20         | 27         | 18         | 51         | 10          | 0.1            |
| 0207691 | 12 mm      | 20         | 27         | 18         | 51         | 10          | 0.1            |
| 0207683 | 13 mm      | 20         | 27         | 18         | 51         | 10          | 0.1            |
| 0207694 | 14 mm      | 20         | 27         | 18         | 51         | 10          | 0.1            |
| 0207684 | 15 mm      | 20         | 27         | 18         | 51         | 10          | 0.1            |
| 0207692 | 16 mm      | 20         | 27         | 18         | 51         | 10          | 0.1            |




## Technical data

| ID      | D1<br>[mm] | D2<br>[mm] | D3<br>[mm] | D4<br>[mm] | L1<br>[mm] | L10<br>[mm] | Weight<br>[kg] |
|---------|------------|------------|------------|------------|------------|-------------|----------------|
| 0207710 | 3 mm       | 22         | 27         | 18         | 53.5       | 10          | 0.1            |
| 0207711 | 4 mm       | 22         | 27         | 18         | 53.5       | 10          | 0.1            |
| 0207712 | 5 mm       | 22         | 27         | 18         | 53.5       | 10          | 0.1            |
| 0207713 | 6 mm       | 22         | 27         | 18         | 53.5       | 10          | 0.1            |
| 0207714 | 7 mm       | 22         | 27         | 18         | 53.5       | 10          | 0.1            |
| 0207715 | 8 mm       | 22         | 27         | 18         | 53.5       | 10          | 0.1            |
| 0207716 | 9 mm       | 22         | 27         | 18         | 53.5       | 10          | 0.1            |
| 0207717 | 10 mm      | 22         | 27         | 18         | 53.5       | 10          | 0.1            |
| 0207718 | 11 mm      | 22         | 27         | 18         | 53.5       | 10          | 0.1            |
| 0207719 | 12 mm      | 22         | 27         | 18         | 53.5       | 10          | 0.1            |
| 0207720 | 13 mm      | 22         | 27         | 18         | 53.5       | 10          | 0.1            |
| 0207721 | 14 mm      | 22         | 27         | 18         | 53.5       | 10          | 0.1            |
| 0207722 | 15 mm      | 22         | 27         | 18         | 53.5       | 10          | 0.1            |
| 0207723 | 16 mm      | 22         | 27         | 18         | 53.5       | 10          | 0.1            |



## Technical data


| ID                      | D1<br>[mm] | D2<br>[mm] | D3<br>[mm] | D4<br>[mm] | L1<br>[mm] | L10<br>[mm] | Weight<br>[kg] |
|-------------------------|------------|------------|------------|------------|------------|-------------|----------------|
| <a href="#">0207695</a> | 6 mm       | 32         | 37         | 20         | 60.5       | 19          | 0.3            |
| <a href="#">0207696</a> | 8 mm       | 32         | 37         | 20         | 60.5       | 19          | 0.3            |
| <a href="#">0207697</a> | 10 mm      | 32         | 37         | 20         | 60.5       | 19          | 0.3            |
| <a href="#">0207698</a> | 12 mm      | 32         | 37         | 20         | 60.5       | 19          | 0.3            |
| <a href="#">0207701</a> | 14 mm      | 32         | 37         | 20         | 60.5       | 19          | 0.3            |
| <a href="#">0207699</a> | 16 mm      | 32         | 37         | 20         | 60.5       | 19          | 0.3            |
| <a href="#">0207702</a> | 18 mm      | 32         | 39         | 22         | 60.5       | 19          | 0.3            |
| <a href="#">0207700</a> | 20 mm      | 32         | 39         | 22         | 60.5       | 19          | 0.3            |
| <a href="#">0207703</a> | 25 mm      | 32         | 44         | 27         | 60.5       | 19          | 0.3            |



Technical data

| ID      | D1<br>[mm] | D2<br>[mm] | D3<br>[mm] | L1<br>[mm] | L2<br>[mm] | L3<br>[mm] | L10<br>[mm] | Weight<br>[kg] |
|---------|------------|------------|------------|------------|------------|------------|-------------|----------------|
| 0207585 | 3 mm       | 20         | 22         | 59         | 50         | 3          | 5           | 0.1            |
| 0207586 | 4 mm       | 20         | 22         | 59         | 50         | 3          | 5           | 0.1            |
| 0207587 | 5 mm       | 20         | 22         | 59         | 50         | 3          | 5           | 0.1            |
| 0207588 | 6 mm       | 20         | 22         | 59         | 50         | 3          | 5           | 0.1            |
| 0207589 | 7 mm       | 20         | 22         | 59         | 50         | 3          | 5           | 0.1            |
| 0207590 | 8 mm       | 20         | 22         | 59         | 50         | 3          | 5           | 0.1            |
| 0207591 | 9 mm       | 20         | 22         | 59         | 50         | 3          | 5           | 0.1            |
| 0207592 | 10 mm      | 20         | 22         | 59         | 50         | 3          | 5           | 0.1            |
| 0207593 | 11 mm      | 20         | 22         | 59         | 50         | 3          | 5           | 0.1            |
| 0207594 | 12 mm      | 20         | 22         | 59         | 50         | 3          | 5           | 0.1            |
| 0207595 | 13 mm      | 20         | 22         | 59         | 50         | 3          | 5           | 0.1            |
| 0207596 | 14 mm      | 20         | 22         | 59         | 50         | 3          | 5           | 0.1            |
| 0207597 | 15 mm      | 20         | 22         | 59         | 50         | 3          | 5           | 0.1            |
| 0207598 | 16 mm      | 20         | 22         | 59         | 50         | 3          | 5           | 0.1            |
| 0207599 | 17 mm      | 20         | 22         | 59         | 50         | 3          | 5           | 0.1            |


Additional sizes and customized designs are available upon request  
Design with bayonet locking



## Technical data

| ID                      | D1<br>[mm] | D2<br>[mm] | D3<br>[mm] | L1<br>[mm] | L2<br>[mm] | L3<br>[mm] | L10<br>[mm] | Weight<br>[kg] |
|-------------------------|------------|------------|------------|------------|------------|------------|-------------|----------------|
| <a href="#">0207605</a> | 6 mm       | 32         | 34         | 69         | 61.5       | 4          | 5           | 0.3            |
| <a href="#">0207606</a> | 8 mm       | 32         | 34         | 69         | 61.5       | 4          | 5           | 0.3            |
| <a href="#">0207607</a> | 10 mm      | 32         | 34         | 69         | 61.5       | 4          | 5           | 0.3            |
| <a href="#">0207608</a> | 12 mm      | 32         | 34         | 69         | 61.5       | 4          | 5           | 0.3            |
| <a href="#">0207609</a> | 14 mm      | 32         | 34         | 69         | 61.5       | 4          | 5           | 0.3            |
| <a href="#">0207610</a> | 16 mm      | 32         | 34         | 69         | 61.5       | 4          | 5           | 0.3            |
| <a href="#">0207611</a> | 18 mm      | 32         | 34         | 69         | 61.5       | 4          | 5           | 0.3            |
| <a href="#">0207612</a> | 20 mm      | 32         | 34         | 69         | 61.5       | 4          | 5           | 0.3            |
| <a href="#">0207613</a> | 25 mm      | 32         | 34         | 69         | 61.5       | 4          | 5           | 0.3            |

Additional sizes and customized designs are available upon request  
Design with bayonet locking




Technical data

| ID      | D1<br>[mm] | D2<br>[mm] | D3<br>[mm] | L1<br>[mm] | L2<br>[mm] | L3<br>[mm] | Weight<br>[kg] |
|---------|------------|------------|------------|------------|------------|------------|----------------|
| 0207615 | 3 mm       | 12         | 14         | 50         | 37.5       | 3          | 0.1            |
| 0207616 | 4 mm       | 12         | 14         | 50         | 37.5       | 3          | 0.1            |
| 0207617 | 5 mm       | 12         | 14         | 50         | 37.5       | 3          | 0.1            |
| 0207618 | 6 mm       | 12         | 14         | 50         | 37.5       | 3          | 0.1            |
| 0207619 | 8 mm       | 12         | 14         | 50         | 37.5       | 3          | 0.1            |

Additional sizes and customized designs are available upon request  
Design with bayonet locking






## Technical data

| ID                      | D1<br>[mm] | D2<br>[mm] | D3<br>[mm] | L1<br>[mm] | L2<br>[mm] | L3<br>[mm] | Weight<br>[kg] |
|-------------------------|------------|------------|------------|------------|------------|------------|----------------|
| <a href="#">0207625</a> | 3 mm       | 20         | 22         | 55.5       | 43         | 3          | 0.1            |
| <a href="#">0207626</a> | 4 mm       | 20         | 22         | 55.5       | 43         | 3          | 0.1            |
| <a href="#">0207628</a> | 6 mm       | 20         | 22         | 55.5       | 43         | 3          | 0.1            |
| <a href="#">0207629</a> | 7 mm       | 20         | 22         | 55.5       | 43         | 3          | 0.1            |
| <a href="#">0207630</a> | 8 mm       | 20         | 22         | 55.5       | 43         | 3          | 0.1            |
| <a href="#">0207631</a> | 9 mm       | 20         | 22         | 55.5       | 43         | 3          | 0.1            |
| <a href="#">0207632</a> | 10 mm      | 20         | 22         | 55.5       | 43         | 3          | 0.1            |
| <a href="#">0207633</a> | 11 mm      | 20         | 22         | 55.5       | 43         | 3          | 0.1            |
| <a href="#">0207634</a> | 12 mm      | 20         | 22         | 55.5       | 43         | 3          | 0.1            |
| <a href="#">0207635</a> | 13 mm      | 20         | 22         | 55.5       | 43         | 3          | 0.1            |
| <a href="#">0207636</a> | 14 mm      | 20         | 22         | 55.5       | 43         | 3          | 0.1            |
| <a href="#">0207637</a> | 15 mm      | 20         | 22         | 55.5       | 43         | 3          | 0.1            |
| <a href="#">0207638</a> | 16 mm      | 20         | 22         | 55.5       | 43         | 3          | 0.1            |
| <a href="#">0207627</a> | 5 mm       | 20         | 22         | 55.5       | 43         | 3          | 0.1            |


Additional sizes and customized designs are available upon request  
Design with bayonet locking



Technical data

| ID      | D1<br>[mm] | D2<br>[mm] | D3<br>[mm] | L1<br>[mm] | L2<br>[mm] | L3<br>[mm] | Weight<br>[kg] |
|---------|------------|------------|------------|------------|------------|------------|----------------|
| 0207645 | 6 mm       | 32         | 34         | 69         | 57.5       | 4          | 0.3            |
| 0207646 | 8 mm       | 32         | 34         | 69         | 57.5       | 4          | 0.3            |
| 0207647 | 10 mm      | 32         | 34         | 69         | 57.5       | 4          | 0.3            |
| 0207648 | 12 mm      | 32         | 34         | 69         | 57.5       | 4          | 0.3            |
| 0207649 | 14 mm      | 32         | 34         | 69         | 57.5       | 4          | 0.3            |
| 0207650 | 16 mm      | 32         | 34         | 69         | 57.5       | 4          | 0.3            |
| 0207651 | 18 mm      | 32         | 34         | 69         | 57.5       | 4          | 0.3            |
| 0207652 | 20 mm      | 32         | 34         | 69         | 57.5       | 4          | 0.3            |
| 0207653 | 25 mm      | 32         | 34         | 69         | 57.5       | 4          | 0.3            |

Additional sizes and customized designs are available upon request  
Design with bayonet locking




## Technical data

| ID                      | D1<br>[mm] | D2<br>[mm] | D3<br>[mm] | D4<br>[mm] | L1<br>[mm] | L2<br>[mm] | L10<br>[mm] | Weight<br>[kg] |
|-------------------------|------------|------------|------------|------------|------------|------------|-------------|----------------|
| <a href="#">0207955</a> | 3 mm       | 12         | 16.5       | 3.5        | 45         | 42.5       | 2           | 0.1            |
| <a href="#">0207956</a> | 4 mm       | 12         | 16.5       | 3.5        | 45         | 42.5       | 2           | 0.1            |
| <a href="#">0207957</a> | 5 mm       | 12         | 16.5       | 3.5        | 45         | 42.5       | 2           | 0.1            |
| <a href="#">0207958</a> | 6 mm       | 12         | 16.5       | 3.5        | 45         | 42.5       | 2           | 0.1            |
| <a href="#">0207959</a> | 8 mm       | 12         | 16.5       | 3.5        | 45         | 42.5       | 2           | 0.1            |

Additional sizes and customized designs are available upon request

Design with radial safety bore – for internal coolant supply/coolant-proof up to max. 80 bar

Run-out accuracy:  $\leq 0.003$  mm




## Technical data

| ID      | D1<br>[mm] | D2<br>[mm] | D3<br>[mm] | D4<br>[mm] | L1<br>[mm] | L2<br>[mm] | L10<br>[mm] | Weight<br>[kg] |
|---------|------------|------------|------------|------------|------------|------------|-------------|----------------|
| 0207965 | 3 mm       | 20         | 24         | 4          | 50.5       | 43         | 2           | 0.1            |
| 0207966 | 4 mm       | 20         | 24         | 4          | 50.5       | 43         | 2           | 0.1            |
| 0207967 | 5 mm       | 20         | 24         | 4          | 50.5       | 43         | 2           | 0.1            |
| 0207968 | 6 mm       | 20         | 24         | 4          | 50.5       | 43         | 2           | 0.1            |
| 0207969 | 7 mm       | 20         | 24         | 4          | 50.5       | 43         | 2           | 0.1            |
| 0207970 | 8 mm       | 20         | 24         | 4          | 50.5       | 43         | 2           | 0.1            |
| 0207971 | 9 mm       | 20         | 24         | 4          | 50.5       | 43         | 2           | 0.1            |
| 0207972 | 10 mm      | 20         | 24         | 4          | 50.5       | 43         | 2           | 0.1            |
| 0207973 | 11 mm      | 20         | 24         | 4          | 50.5       | 43         | 2           | 0.1            |
| 0207974 | 12 mm      | 20         | 24         | 4          | 50.5       | 43         | 2           | 0.1            |
| 0207975 | 13 mm      | 20         | 24         | 4          | 50.5       | 43         | 2           | 0.1            |
| 0207976 | 14 mm      | 20         | 24         | 4          | 50.5       | 43         | 2           | 0.1            |
| 0207977 | 15 mm      | 20         | 24         | 4          | 50.5       | 43         | 2           | 0.1            |
| 0207978 | 16 mm      | 20         | 24         | 4          | 50.5       | 43         | 2           | 0.1            |

Additional sizes and customized designs are available upon request

Design with radial safety bore – for internal coolant supply/coolant-proof up to max. 80 bar

Run-out accuracy:  $\leq 0.003$  mm




## Technical data

| ID                      | D1<br>[mm] | D2<br>[mm] | D3<br>[mm] | D4<br>[mm] | L1<br>[mm] | L2<br>[mm] | L10<br>[mm] | Weight<br>[kg] |
|-------------------------|------------|------------|------------|------------|------------|------------|-------------|----------------|
| <a href="#">0207885</a> | 6 mm       | 22         | 25         | 4          | 50.5       | 46         | 2           | 0.2            |
| <a href="#">0207886</a> | 8 mm       | 22         | 25         | 4          | 50.5       | 46         | 2           | 0.2            |
| <a href="#">0207887</a> | 10 mm      | 22         | 25         | 4          | 50.5       | 46         | 2           | 0.2            |
| <a href="#">0207888</a> | 12 mm      | 22         | 25         | 4          | 50.5       | 46         | 2           | 0.2            |
| <a href="#">0207889</a> | 14 mm      | 22         | 25         | 4          | 50.5       | 46         | 2           | 0.2            |
| <a href="#">0207890</a> | 16 mm      | 22         | 25         | 4          | 50.5       | 46         | 2           | 0.2            |

Additional sizes and customized designs are available upon request

Design with radial safety bore – for internal coolant supply/coolant-proof up to max. 80 bar

Run-out accuracy:  $\leq 0.003$  mm



Technical data

| ID      | D1<br>[mm] | D2<br>[mm] | D3<br>[mm] | D4<br>[mm] | L1<br>[mm] | L2<br>[mm] | L10<br>[mm] | Weight<br>[kg] |
|---------|------------|------------|------------|------------|------------|------------|-------------|----------------|
| 0207985 | 6 mm       | 32         | 35.5       | 4          | 60.5       | 53.5       | 2           | 0.3            |
| 0207986 | 8 mm       | 32         | 35.5       | 4          | 60.5       | 53.5       | 2           | 0.3            |
| 0207987 | 10 mm      | 32         | 35.5       | 4          | 60.5       | 53.5       | 2           | 0.3            |
| 0207988 | 12 mm      | 32         | 35.5       | 4          | 60.5       | 53.5       | 2           | 0.3            |
| 0207989 | 14 mm      | 32         | 35.5       | 4          | 60.5       | 53.5       | 2           | 0.3            |
| 0207990 | 16 mm      | 32         | 35.5       | 4          | 60.5       | 53.5       | 2           | 0.3            |
| 0207991 | 18 mm      | 32         | 35.5       | 4          | 60.5       | 53.5       | 2           | 0.3            |
| 0207992 | 20 mm      | 32         | 35.5       | 4          | 60.5       | 53.5       | 2           | 0.3            |
| 0207993 | 25 mm      | 32         | 35.5       | 4          | 60.5       | 53.5       | 2           | 0.3            |

Additional sizes and customized designs are available upon request  
Design with radial safety bore - for internal coolant supply/coolant-proof up to max. 80 bar  
Run-out accuracy: ≤ 0.003 mm





**SCHUNK SE & Co. KG**

**Spanntechnik**

**Greiftechnik**

**Automatisierungstechnik**

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

[CMS@de.schunk.com](mailto:CMS@de.schunk.com)

[schunk.com](http://schunk.com)