


**TENDO WZS**



**Presnosť hádzania**  
< 0,003 mm\*



**Kvalita vyváženia**  
G2.5 pri 25 000 ot./min\*



**Krátka doba osádzania**



**Otvor pre dátový nosič**  
voliteľne možné



**Vnútorné chladenie**  
do 80 bar


## Technické údaje

| ID                      | D1<br>[mm] | D2<br>[mm] | D3<br>[mm] | D6<br>[mm] | L1<br>[mm] | L2<br>[mm] | L4<br>[mm] | L5<br>[mm] | G     | Mmin<br>[Nm] | Hmotnosť<br>[kg] |                         |
|-------------------------|------------|------------|------------|------------|------------|------------|------------|------------|-------|--------------|------------------|-------------------------|
| <a href="#">0219221</a> | 6 mm       | 32         | 60         | 15         | 110        | 43         | 55         | 90.9       | M5    | 4            | 3.6              | <a href="#">9205640</a> |
| <a href="#">0219222</a> | 8 mm       | 33.5       | 60         | 17         | 110        | 43         | 55         | 90.9       | M6    | 7            | 3.6              | <a href="#">9205640</a> |
| <a href="#">0219223</a> | 10 mm      | 35         | 60         | 19         | 110        | 43         | 55         | 90.9       | M8x1  | 14           | 3.7              | <a href="#">9205640</a> |
| <a href="#">0219224</a> | 12 mm      | 36.5       | 60         | 21.5       | 110        | 50         | 55         | 90.9       | M8x1  | 22           | 3.7              | <a href="#">9205640</a> |
| <a href="#">0219229</a> | 14 mm      | 38         | 60         | 23.5       | 110        | 50         | 60         | 90.9       | M10x1 | 35           | 3.7              | <a href="#">9205640</a> |
| <a href="#">0219225</a> | 16 mm      | 39.5       | 60         | 25.5       | 110        | 53         | 60         | 90.9       | M12x1 | 50           | 3.8              | <a href="#">9205640</a> |
| <a href="#">0219220</a> | 18 mm      | 41         | 60         | 27.5       | 110        | 53         | 60         | 90.9       | M12x1 | 70           | 3.8              | <a href="#">9205640</a> |
| <a href="#">0219226</a> | 20 mm      | 42         | 70         | 28         | 110        | 95         | 47         | 90.9       | M16x1 | 90           | 3.9              | <a href="#">9205640</a> |
| <a href="#">0219227</a> | 22 mm      | 44         | 70         | 30         | 110        | 95         | 49         | 90.9       | M16x1 | 100          | 3.9              | <a href="#">9205640</a> |
| <a href="#">0219228</a> | 32 mm      | 54         | 70         | 40         | 110        | 95         | 62.5       | 90.9       | M16x1 | 250          | 4                | <a href="#">9205640</a> |

\*Presnosť radiálne vystredneného chodu: na úrovni 2,5 x D

\*Kvalita vyváženia: alebo  $U_{max} < 1 \text{ gmm}$

Ďalšie veľkosti a prispôbené vyhotovenia sú k dispozícii na vyžiadanie



**Presnosť hádzania**  
< 0,003 mm\*



**Kvalita vyváženia**  
G2.5 pri 25 000 ot./min\*



**Krátka doba osádzania**



**Otvor pre dátový nosič**  
voliteľne možné



**Vnútorné chladienie**  
do 80 bar


## Technické údaje

| ID                       | D1<br>[Inch] | D2<br>[mm] | D3<br>[mm] | D6<br>[mm] | L1<br>[mm] | L2<br>[mm] | L3<br>[mm] | L4<br>[mm] | L5<br>[mm] | G     | Mmin<br>[Nm] | Hmotnosť<br>[kg] |                         |
|--------------------------|--------------|------------|------------|------------|------------|------------|------------|------------|------------|-------|--------------|------------------|-------------------------|
| <a href="#">28000629</a> | 3/8"         | 30.5       | 69.85      | 16         | 111        | 44.8       | 10         | 35         | 79         | M6    | 11           | 2.7              | <a href="#">9205640</a> |
| <a href="#">28000630</a> | 1/2"         | 36         | 69.85      | 20         | 111        | 46         | 10         | 37         | 79         | M10x1 | 30           | 2.7              | <a href="#">9205640</a> |
| <a href="#">28000631</a> | 5/8"         | 36.8       | 69.85      | 22         | 111        | 47.5       | 10         | 39         | 79         | M10x1 | 50           | 2.7              | <a href="#">9205640</a> |
| <a href="#">28000632</a> | 3/4"         | 42         | 69.85      | 28         | 111        | 52         | 10         | 41         | 79         | M16x1 | 80           | 2.8              | <a href="#">9205640</a> |
| <a href="#">28000633</a> | 7/8"         | 45.2       | 69.85      | 31         | 111        | 52         | 10         | 41         | 79         | M16x1 | 100          | 2.8              | <a href="#">9205640</a> |
| <a href="#">28000634</a> | 1"           | 48         | 69.85      | 34         | 111        | 63         | 10         | 52         | 79         | M16x1 | 180          | 2.8              | <a href="#">9205640</a> |
| <a href="#">28000635</a> | 1 1/4"       | 54         | 69.85      | 40         | 111        | 63         | 10         | 55.5       | 79         | M16x1 | 250          | 4.4              | <a href="#">9205640</a> |

\*Presnosť radiálne vystredeneného chodu: na úrovni 2,5 x D

\*Kvalita vyváženia: alebo U<sub>max</sub> < 1 gmm

Ďalšie veľkosti a prispôsobené vyhotovenia sú k dispozícii na vyžiadanie



**Presnosť hádzania**  
< 0,003 mm\*



**Kvalita vyváženia**  
G2.5 pri 25 000 ot./min\*



**Krátka doba osádzania**



**Otvor pre dátový nosič**  
voliteľne možné



**Vnútorné chladenie**  
do 80 bar


## Technické údaje

| ID                       | D1<br>[mm/Inch] | D2<br>[mm] | D3<br>[mm] | D6<br>[mm] | L<br>[mm] | L2<br>[mm] | L4<br>[mm] | L5<br>[mm] | Mmin<br>[Nm] | Hmotnosť<br>[kg] |                         |
|--------------------------|-----------------|------------|------------|------------|-----------|------------|------------|------------|--------------|------------------|-------------------------|
| <a href="#">28000061</a> | 20 mm           | 54         |            | 40.7       | 72        | 72         | 44         |            | 90           | 1.9              | <a href="#">9205650</a> |
| <a href="#">28000062</a> | 32 mm           | 54         |            | 52.2       | 82        | 82         | 54         |            | 250          | 1.9              | <a href="#">9205660</a> |
| <a href="#">28003756</a> | 12 mm           | 36.5       | 70         | 21.5       | 111       |            | 41         | 73         | 22           | 3                | <a href="#">9205640</a> |
| <a href="#">28003757</a> | 20 mm           | 42         | 70         | 28         | 111       |            | 47.4       | 73         | 90           | 3                | <a href="#">9205640</a> |
| <a href="#">28003758</a> | 32 mm           | 54         | 70         | 40         | 111       |            | 55         | 73         | 250          | 3                | <a href="#">9205640</a> |
| <a href="#">28000056</a> | 3/4"            | 54         |            | 40.7       | 72        | 72         | 44         |            | 80           | 1.9              | <a href="#">9205650</a> |
| <a href="#">28000057</a> | 1"              | 54         |            | 46.7       | 75        | 75         | 47         |            | 180          | 1.9              | <a href="#">9205660</a> |
| <a href="#">28000059</a> | 1 1/4"          | 54         |            | 52.2       | 82        | 82         | 54         |            | 250          | 1.9              | <a href="#">9205660</a> |
| <a href="#">28003746</a> | 1/2"            | 36         | 70         | 20         | 111       |            | 37         | 73         | 30           | 3                | <a href="#">9205640</a> |
| <a href="#">28003747</a> | 3/4"            | 42         | 70         | 28         | 111       |            | 41         | 73         | 80           | 3                | <a href="#">9205640</a> |
| <a href="#">28003748</a> | 1 1/4"          | 54         | 70         | 40         | 111       |            | 55         | 73         | 250          | 3                | <a href="#">9205640</a> |

\*Presnosť radiálne vystredené chodu: na úrovni 2,5 x D

\*Kvalita vyváženia: alebo U<sub>max</sub> < 1 gmm

Ďalšie veľkosti a prispôbené vyhotovenia sú k dispozícii na vyžiadanie



**Krátka doba  
osádzania**



**Otvor pre dátový  
nosič**  
voliteľne možné





**Vnútorne chladenie**  
do 80 bar

## Technické údaje

| ID                       | Rozhranie | L1<br>[mm] | L4<br>[mm] | L5<br>[mm] | G     | Hmotnosť<br>[kg] |
|--------------------------|-----------|------------|------------|------------|-------|------------------|
| <a href="#">28000184</a> | CAT 40    | 54         | 19         | 35         | M16x1 | 2.021            |
| <a href="#">28000185</a> | CAT 50    | 56         | 21         | 37         | M16x1 | 4.166            |

Ďalšie veľkosti a prispôsobené vyhotovenia sú k dispozícii na vyžiadanie



**Presnosť hádzania**  
< 0,003 mm\*



**Kvalita vyváženia**



**Krátka doba osádzania**



**Optimalizované  
rušivé kontúry**




**Vnútorné chladenie**

## Technické údaje

| ID                       | D1<br>[mm] | D2<br>[mm] | Ø6<br>[mm] | L1<br>[mm] | L2<br>[mm] | L4<br>[mm] | L10<br>[mm] | L11<br>[mm] | Hmotnosť<br>[kg] |
|--------------------------|------------|------------|------------|------------|------------|------------|-------------|-------------|------------------|
| <a href="#">20059729</a> | 12 mm      | 36.5       | 21.5       | 84         | 60         | 43         | 5.5         | 31.1        | 2.3              |
| <a href="#">20056776</a> | 20 mm      | 42         | 28         | 84         | 60         | 46         | 5.5         | 31.5        | 2.3              |
| <a href="#">20060231</a> | 25 mm      | 47         | 33         | 84         | 60         | 48.5       | 5.5         | 35          | 2.3              |
| <a href="#">20063191</a> | 32 mm      | 54         | 40         | 90         | 70         | 56         | 5.5         | 42          | 2.4              |

\*Presnosť radiálne vystredeného chodu: na úrovni 2,5 x D



**Presnosť hádzania**  
< 0,003 mm\*



**Kvalita vyváženia**



**Krátka doba osádzania**



**Optimalizované rušivé kontúry**





**Vnútorné chladenie**

## Technické údaje

| ID      | D1<br>[mm] | D2<br>[mm] | D6<br>[mm] | L1<br>[mm] | L2<br>[mm] | L4<br>[mm] | L10<br>[mm] | L11<br>[mm] | Hmotnosť<br>[kg] |
|---------|------------|------------|------------|------------|------------|------------|-------------|-------------|------------------|
| 0206746 | 12 mm      | 36.5       | 21.5       | 111        | 50         | 52         | 5.5         | 32.1        | 3.3              |
| 0206747 | 20 mm      | 42         | 28         | 121        | 60         | 62         | 5.5         | 31.5        | 3.4              |
| 0206748 | 22 mm      | 44         | 30         | 126        | 60         | 62         | 5.5         | 35.5        | 3.5              |
| 0206749 | 32 mm      | 54         | 40         | 131        | 70         | 72         | 6           | 42.5        | 3.8              |

\*Presnosť radiálne vystredeneného chodu: na úrovni 2,5 x D



**Presnosť hádzania**  
< 0,003 mm\*



**Kvalita vyváženia**



**Krátka doba osádzania**



**Optimalizované  
rušivé kontúry**





**Vnútrorné chladenie**

## Technické údaje

| ID      | D1<br>[mm] | D2<br>[mm] | D6<br>[mm] | L<br>[mm] | L1<br>[mm] | L2<br>[mm] | L4<br>[mm] | L10<br>[mm] | L11<br>[mm] | Hmotnosť<br>[kg] |
|---------|------------|------------|------------|-----------|------------|------------|------------|-------------|-------------|------------------|
| 0206766 | 12 mm      | 36.5       | 21.5       | 125       | 87         |            | 75         | 5.5         | 32.1        | 1.3              |
| 0206767 | 20 mm      | 42         | 28         | 125       | 87         |            | 75         | 5.5         | 31.5        | 1.4              |
| 0206768 | 22 mm      | 44         | 30         | 125       | 87         | 61         | 75         | 5.5         | 35.5        | 1.5              |
| 0206769 | 32 mm      | 54         | 40         | 125       | 87         | 61         | 75         | 6           | 42.5        | 1.6              |

\*Presnosť radiálne vystredeného chodu: na úrovni 2,5 x D





**Presnosť hádzania**  
 $< 0,003 \text{ mm}^*$



**Kvalita vyváženia**



**Krátka doba osádzania**



**Optimalizované rušivé kontúry**





**Vnútorné chladenie**

## Technické údaje

| ID      | D1<br>[mm] | D2<br>[mm] | D3<br>[mm] | D6<br>[mm] | L<br>[mm] | L1<br>[mm] | L2<br>[mm] | L4<br>[mm] | L5<br>[mm] | L10<br>[mm] | L11<br>[mm] | Hmotnosť<br>[kg] |
|---------|------------|------------|------------|------------|-----------|------------|------------|------------|------------|-------------|-------------|------------------|
| 0206671 | 12 mm      | 36.5       | 54         | 21.5       | 130.6     | 90         | 64         | 47         | 68         | 5.5         | 32.1        | 3.12             |
| 0206660 | 12 mm      | 36.5       | 54         | 21.5       | 180.6     | 140        | 64         | 70         | 118        | 5.5         | 32.1        | 3.7              |
| 0206672 | 20 mm      | 42         | 54         | 28         | 130.6     | 90         | 64         | 53         | 68         | 5.5         | 31.5        | 3.12             |
| 0206661 | 20 mm      | 42         | 54         | 28         | 180.6     | 140        | 64         | 70         | 118        | 5.5         | 31.5        | 3.85             |
| 0206673 | 22 mm      | 44         | 54         | 30         | 130.6     | 90         | 64         | 53         | 68         | 5.5         | 35.5        | 3.15             |
| 0206662 | 22 mm      | 44         | 54         | 30         | 180.6     | 140        | 64         | 70         | 118        | 5.5         | 35.5        | 3.9              |
| 0206674 | 32 mm      | 54         |            | 40         | 130.6     | 90         | 70         |            | 68         | 6           | 42.5        | 3.22             |
| 0206663 | 32 mm      | 54         |            | 40         | 180.6     | 140        | 70         |            | 118        | 6           | 42.5        | 4.1              |

\*Presnosť radiálne vystredného chodu: na úrovni 2,5 x D



**Presnosť hádzania**  
 $< 0,003 \text{ mm}^*$



## Kvalita vyváženia



## Krátka doba osádzania



## Optimalizované rušivé kontúry





## Vnútročné chladenie

## Technické údaje

| ID      | D1<br>[mm] | D2<br>[mm] | D6<br>[mm] | L<br>[mm] | L10<br>[mm] | L11<br>[mm] | Hmotnosť<br>[kg] |
|---------|------------|------------|------------|-----------|-------------|-------------|------------------|
| 0206696 | 12 mm      | 36.5       | 21.5       | 115       | 5.5         | 32.1        | 3.2              |
| 0206697 | 20 mm      | 42         | 28         | 115       | 5.5         | 31.5        | 3.3              |
| 0206698 | 22 mm      | 44         | 30         | 115       | 5.5         | 35.5        | 3.4              |
| 0206699 | 32 mm      | 54         | 40         | 115       | 6           | 42.5        | 3.5              |

\*Presnosť radiálne vystredeného chodu: na úrovni  $2,5 \times D$



**Presnosť hádzania**  
 $< 0,003 \text{ mm}^*$



**Kvalita vyváženia**



**Krátka doba osádzania**



**Optimalizované rušivé kontúry**




**Vnúťorné chladenie**

## Technické údaje

| ID      | D1<br>[mm] | D2<br>[mm] | D3<br>[mm] | D6<br>[mm] | L1<br>[mm] | L2<br>[mm] | L4<br>[mm] | L5<br>[mm] | L10<br>[mm] | L11<br>[mm] | G     | Hmotnosť<br>[kg] |
|---------|------------|------------|------------|------------|------------|------------|------------|------------|-------------|-------------|-------|------------------|
| 0206645 | 12 mm      | 36.5       | 45         | 21.5       | 59         | 50         | 33         | 46         | 5.5         | 25.6        | M8x1  | 1.6              |
| 0206646 | 20 mm      | 42         | 49.5       | 28         | 70         | 60         | 44         | 57         | 5.5         | 31.5        | M12x1 | 1.8              |
| 0206647 | 22 mm      | 44         | 53         | 30         | 77         | 70         | 45         | 64         | 5.5         | 35.5        | M12x1 | 1.9              |
| 0206648 | 32 mm      | 54         | 57         | 40         | 82         | 75         | 59         | 69         | 6           | 42.5        | M12x1 | 2.1              |

\*Presnosť radiálne vystredeneného chodu: na úrovni  $2,5 \times D$



**Presnosť hádzania**  
 $< 0,003 \text{ mm}^*$



**Kvalita vyváženia**



**Krátka doba osádzania**



**Optimalizované rušivé kontúry**





**Vnútorné chladenie**

## Technické údaje

| ID                      | D1<br>[mm] | D2<br>[mm] | D6<br>[mm] | L<br>[mm] | L2<br>[mm] | L4<br>[mm] | L5<br>[mm] | L10<br>[mm] | L11<br>[mm] | Hmotnosť<br>[kg] |
|-------------------------|------------|------------|------------|-----------|------------|------------|------------|-------------|-------------|------------------|
| <a href="#">0206686</a> | 12 mm      | 36.5       | 21.5       | 90        |            | 39         | 75         | 5.5         | 32.1        | 1.3              |
| <a href="#">0206687</a> | 20 mm      | 42         | 28         | 90        |            | 45         | 73         | 5.5         | 31.5        | 1.4              |
| <a href="#">0206688</a> | 22 mm      | 44         | 30         | 90        | 70         | 45         | 75         | 5.5         | 35.5        | 1.5              |
| <a href="#">0206689</a> | 32 mm      | 54         | 40         | 90        | 70         | 58         | 75         | 6           | 42.5        | 1.6              |

\*Presnosť radiálne vystredeneného chodu: na úrovni  $2,5 \times D$



**Presnosť hádzania**  
< 0,003 mm\*



**Kvalita vyváženia**



**Krátka doba osádzania**



**Optimalizované rušivé kontúry**





**Vnútorné chladenie**

## Technické údaje

| ID      | D1<br>[mm] | D2<br>[mm] | D4<br>[mm] | L1<br>[mm] | L2<br>[mm] | L5<br>[mm] | L6<br>[mm] | L8<br>[mm] | X<br>[mm] | G     | Hmotnosť<br>[kg] |
|---------|------------|------------|------------|------------|------------|------------|------------|------------|-----------|-------|------------------|
| 0206626 | 12 mm      | 36.5       | 21.5       | 80         | 54         | 5.5        | 25.6       | 53         | 26        | M8x1  | 2.9              |
| 0206627 | 20 mm      | 42         | 28         | 80         | 56.5       | 5.5        | 31.5       | 56.5       | 23.5      | M10x1 | 3.1              |
| 0206628 | 22 mm      | 44         | 30         | 80         | 54         | 5.5        | 35.5       | 56.5       | 26        | M10x1 | 3.2              |
| 0206629 | 32 mm      | 54         | 40         | 80.5       | 69.5       | 6          | 42.5       | 62.5       | 24        | M10x1 | 3.3              |

\*Presnosť radiálne vystredeneného chodu: na úrovni 2,5 x D



**Presnosť hádzania**  
 $< 0,003 \text{ mm}^*$



**Kvalita vyváženia**



**Krátka doba osádzania**



**Optimalizované  
 rušivé kontúry**




**Vnútročné chladenie**

## Technické údaje

| ID                      | D1<br>[mm] | D2<br>[mm] | D4<br>[mm] | L1<br>[mm] | L2<br>[mm] | L5<br>[mm] | L6<br>[mm] | L8<br>[mm] | L9<br>[mm] | X<br>[mm] | $\alpha$<br>[°] | Hmotnosť<br>[kg] |
|-------------------------|------------|------------|------------|------------|------------|------------|------------|------------|------------|-----------|-----------------|------------------|
| <a href="#">0206776</a> | 12 mm      | 36.5       | 21.5       | 94         | 62         | 5.5        | 32.1       | 45         | 104        | 32        | 45              | 1.7              |
| <a href="#">0206777</a> | 20 mm      | 42         | 38         | 94         | 62         | 5.5        | 31.5       | 47         | 104        | 32        | 45              | 1.8              |
| <a href="#">0206778</a> | 22 mm      | 44         | 30         | 94         | 62         | 5.5        | 35.5       | 47         | 104        | 32        | 45              | 1.9              |
| <a href="#">0206779</a> | 32 mm      | 54         | 40         | 94         | 62         | 6          | 42.5       | 69         | 104        | 32        | 90              | 2                |

\*Presnosť radiálne vystredeneného chodu: na úrovni  $2,5 \times D$



**Presnosť hádzania**  
< 0,003 mm\*



**Kvalita vyváženia**



**Krátka doba  
osádzania**



**Optimalizované  
rušivé kontúry**





**Vnútorné chladenie**

## Technické údaje

| ID                      | D1<br>[mm] | D2<br>[mm] | D4<br>[mm] | L1<br>[mm] | L2<br>[mm] | L5<br>[mm] | L6<br>[mm] | L7<br>[mm] | L9<br>[mm] | X<br>[mm] | Hmotnosť<br>[kg] |
|-------------------------|------------|------------|------------|------------|------------|------------|------------|------------|------------|-----------|------------------|
| <a href="#">0206676</a> | 12 mm      | 36.5       | 21.5       | 90         | 52.5       | 5.5        | 32.1       | 70         | 191.6      | 37.5      | 2.7              |
| <a href="#">0206677</a> | 20 mm      | 42         | 28         | 90         | 52.5       | 5.5        | 31.5       | 70         | 191.6      | 37.5      | 2.9              |
| <a href="#">0206678</a> | 22 mm      | 44         | 30         | 90         | 55         | 5.5        | 35.5       | 70         | 191.6      | 37.5      | 3                |
| <a href="#">0206679</a> | 32 mm      | 54         | 40         | 100        | 65         | 6          | 42.5       | 80         | 201.6      | 35        | 3.1              |

\*Presnosť radiálne vystredeneného chodu: na úrovni 2,5 x D



**Presnosť hádzania**  
 $< 0,003 \text{ mm}^*$



**Kvalita vyváženia**



**Krátka doba osádzania**



**Optimalizované rušivé kontúry**



**Vnútorné chladenie**

## Technické údaje

| ID      | D1<br>[mm] | D2<br>[mm] | D3<br>[mm] | D4<br>[mm] | L1<br>[mm] | L2<br>[mm] | L5<br>[mm] | L6<br>[mm] | L7<br>[mm] | L8<br>[mm] | X<br>[mm] | Hmotnosť<br>[kg] |
|---------|------------|------------|------------|------------|------------|------------|------------|------------|------------|------------|-----------|------------------|
| 0206606 | 12 mm      | 36.5       |            | 21.5       | 90         | 50         | 5.5        | 32.1       |            | 70         | 40        | 2.7              |
| 0206607 | 20 mm      | 42         |            | 28         | 90         | 64         | 5.5        | 31.5       |            | 70         | 26        | 2.9              |
| 0206608 | 22 mm      | 44         |            | 30         | 90         | 64         | 5.5        | 35.5       |            | 70         | 26        | 3                |
| 0206609 | 32 mm      | 54         |            | 40         | 90         | 70         | 6          | 42.5       |            | 70         | 20        | 3.1              |
| 0206616 | 12 mm      | 36.5       | 54         | 21.5       | 140        | 50         | 5.5        | 32.1       | 70         | 120        | 90        | 3.4              |
| 0206617 | 20 mm      | 42         | 54         | 28         | 140        | 64         | 5.5        | 31.5       | 70         | 120        | 76        | 3.6              |
| 0206618 | 22 mm      | 44         | 54         | 30         | 140        | 64         | 5.5        | 35.5       | 70         | 120        | 76        | 3.7              |
| 0206619 | 32 mm      | 54         |            | 40         | 140        | 70         | 6          | 42.5       |            | 120        | 70        | 3.8              |

\*Presnosť radiálne vystredného chodu: na úrovni  $2,5 \times D$







**SCHUNK SE & Co. KG**

**Spanntechnik**

**Greiftechnik**

**Automatisierungstechnik**

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

[CMS@de.schunk.com](mailto:CMS@de.schunk.com)

[schunk.com](http://schunk.com)