



TRIBOS SRE




기술 데이터

설명	ID	클램핑 지름용	D2 [mm]	L1 [mm]	중량 [kg]	스페어 링 소형	스페어 링 대형
TRIBOS-R SRE 25	0201978	Ø6	25	35	0.735	9936839	9936840
TRIBOS-R SRE 28	0201980	Ø8, Ø1/4"	28	35	0.699	9936839	9936840
TRIBOS-R SRE 35	0201982	Ø10, Ø3/8"	35	40	0.641	9936839	9936840
TRIBOS-R SRE 42	0201983	Ø12	42	45	0.555	9936839	9936840
TRIBOS-R SRE 48	0201984	Ø14-Ø20, Ø1/2", Ø5/8", Ø3/4"	48	45	0.658	9936839	9936840
TRIBOS-R SRE 60	0201921	Ø25, Ø1"	60	45	0.319	9942628	7008661
TRIBOS-R SRE 67	0201922	Ø32, Ø1 1/4"	67	45	0.212	9942628	7008661




기술 데이터

설명	ID	클램핑 지름용	D2 [mm]	L1 [mm]	중량 [kg]	스페어 링 소형	스페어 링 대형
TRIBOS-RM SRE 20	0201892	Ø3-Ø12	20	27.2	0.871	9936839	9936840
TRIBOS-RM SRE 25	0201893	Ø3-Ø6	25	35	0.5	9936839	9936840




기술 데이터

설명	ID	클램핑 지름용	D2 [mm]	L1 [mm]	중량 [kg]	스페어 링 소형	스페어 링 대형
TRIBOS-S SRE 10	0201972	Ø6	10	35	0.915	9936839	9936840
TRIBOS-S SRE 10.3	0201988	Ø1/4"	10.3	35	0.5	9936839	9936840
TRIBOS-S SRE 13	0201973	Ø8, Ø5/16"	13	35	0.878	9936839	9936840
TRIBOS-S SRE 15	0201989	Ø3/8"	15	45	0.45	9936839	9936840
TRIBOS-S SRE 16	0201974	Ø10	16	40	0.895	9936839	9936840
TRIBOS-S SRE 17.8	0201990	Ø7/16"	17.8	45	0.4	9936839	9936840
TRIBOS-S SRE 19	0201975	Ø12	19	45	0.91	9936839	9936840
TRIBOS-S SRE 20	0201991	Ø1/2"	20	45	0.4	9936839	9936840
TRIBOS-S SRE 22	0201976	Ø14	22	45	0.86	9936839	9936840
TRIBOS-S SRE 25	0201977	Ø16, Ø5/8"	25	45	0.815	9936839	9936840
TRIBOS-S SRE 28	0201979	Ø18	28	45	0.769	9936839	9936840
TRIBOS-S SRE 29	0201992	Ø3/4"	29	45	0.35	9936839	9936840
TRIBOS-S SRE 30	0201981	Ø20	30	45	0.737	9936839	9936840
TRIBOS-S SRE 36	0201987	Ø25	36	45	0.645	9936839	9936840
TRIBOS-S SRE 36.5	0201993	Ø1"	36.5	45	0.35	9936839	9936840
TRIBOS-S SRE 45	0201998	Ø32, Ø1 1/4"	45	45	0.506	9936839	9936840




기술 데이터

설명	ID	클램핑 지름용	D2 [mm]	L1 [mm]	중량 [kg]	스페어 링 소형	스페어 링 대형
TRIBOS-Mini SRE 6.65	25005968	Ø1-Ø4, Ø1/8", Ø3/16"	6.65	17.5	0.8	9936839	9936840
TRIBOS-Mini SRE 9	0201971	Ø0.3-Ø6, Ø1/8", Ø3/16"	9	22.5	0.743	9936839	9936840



기술 데이터

설명	ID	클램핑 지름용	D2 [mm]	L1 [mm]	중량 [kg]	스페어 링 소형	스페어 링 대형
TRIBOS-R SRE SO 25	25000593	Ø6	25	45	0.5	9938251	9938252
TRIBOS-R SRE SO 28	25000594	Ø8, Ø1/4"	28	45	0.45	9938251	9938252
TRIBOS-R SRE SO 48	25000596	Ø14-Ø20, Ø1/2", Ø5/8", Ø3/4"	48	45	0.3	9938251	9938252



기술 데이터

설명	ID	클램핑 지름용	D2 [mm]	L1 [mm]	중량 [kg]	스페어 링 소형	스페어 링 대형
TRIBOS-S SRE SO 10	0206081	Ø6	10	35	0.65	9938251	9938252
TRIBOS-S SRE SO 10.3	25001067	Ø1/4"	10.3	45	0.5	9938251	9938252
TRIBOS-S SRE SO 13	0206082	Ø8, Ø5/16"	13	35	0.35	9938251	9938252
TRIBOS-S SRE SO 15	25000996	Ø3/8"	15	45	0.3	9938251	9938252
TRIBOS-S SRE SO 16	0206083	Ø10	16	40	0.35	9938251	9938252
TRIBOS-S SRE SO 19	0206084	Ø12	19	45	0.4	9938251	9938252
TRIBOS-S SRE SO 20	25000910	Ø1/2"	20	45	0.3	9938251	9938252
TRIBOS-S SRE SO 22	0206085	Ø14	22	45	0.35	9938251	9938252
TRIBOS-S SRE SO 25	0206086	Ø16, Ø5/8"	25	45	0.3	9938251	9938252
TRIBOS-S SRE SO 28	0206087	Ø18	28	45	0.35	9938251	9938252
TRIBOS-S SRE SO 29	25001026	Ø3/4"	29	45	0.3	9938251	9938252
TRIBOS-S SRE SO 30	0206088	Ø20	30	45	0.35	9938251	9938252
TRIBOS-S SRE SO 35	0206089	Ø25	35	45	0.4	9938251	9938252
TRIBOS-S SRE SO 36	0206090	Ø25	36	45	0.32	9938251	9938252
TRIBOS-S SRE SO 36.5	25001684	Ø1"	36.5	45	0.8	9938251	9938252
TRIBOS-S SRE SO 45	0206091	Ø32, Ø1 1/4"	45	45	0.32	9938251	9938252



SCHUNK SE & Co. KG
Spanntechnik
Greiftechnik
Automatisierungstechnik

Bahnhofstr. 106 - 134
D-74348 Lauffen/Neckar
Tel. +49-7133-103-0
Fax +49-7133-103-2399
CMS@de.schunk.com
schunk.com